

PLOCHÁ A ČTYŘHRANNÁ OCEL, PODLE DIN 59350

2922.2842.



Materiál:


1.2842 / 90 MnCrV
ocel pro práci zastudena

Provedení:

tloušťka přesně broušená, šířka broušená nebo frézovaná, délka opracovaná

Upozornění:

- = lze dodat v délce 500 mm a 1000 mm
- = lze dodat pouze v délce 500 mm



2922.2842. Plochá a čtyřhranná ocel, podle DIN 59350

s	1	2	3	4	5	6	8	10	12	15	16	20	25	30	40	50	60
b																	
4				○													
5					○												
6						●											
8							●										
10	○	●	●	●	●	●	●	●									
12	○	●	●	●	●	●	●	●	●								
15	○	●	●	●	●	●	●	●	●	●							
16											●						
20	○	●	●	●	●	●	●	●	●	●		●					
25	○	●	●	●	●	●	●	●	●	●		●	●				
30	○	●	●	●	●	●	●	●	●	●		●	●	●			
35	○	●	●	●	●	●	●	●	●	●		●	●	●			
40	○	●	●	●	●	●	●	●	●	●		●	●	●	●		
50	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	
60	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
70	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
80	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
100	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
120	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
125	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
150	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
160	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
180	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
200	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
250	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●
300	○	●	●	●	●	●	●	●	●	●		●	●	●	●	●	●

Příklad objednávky:

Plochá a čtyřhranná ocel, podle DIN 59350	=	2922.2842.
Šířka B	50 mm =	050.
Tloušťka S	1 mm =	001.
Délka L	500 mm =	0500
Objednací číslo	=	2922.2842. 050.001.0500