

# PRECISION FLAT AND SQUARE BAR STEEL WITH MACHINING ALLOWANCE, DIN 59350

## Material:

1.2343 / X 37 CrMoV 5-1  
Hot work steel

2923.2343.




we deliver original  
**BÖHLER**  
quality

## Execution:

Thickness precision ground, width ground or milled, length machined

## Note:

- = available in 500 mm and 1000 mm lengths
- = only available in 500 mm lengths
- = only available in 1000 mm lengths



## 2923.2343. Precision flat and square bar steel with machining allowance, DIN 59350

s	4.2	5.2	6.2	8.2	10.4	12.4	15.4	16.4	20.4	25.4	30.4	32.4	40.4	50.4	60.4	80.4	100.4
10.3	○	○	○	○													
10.4					○												
12.4						○											
15.3	○	○	○	○	○	○											
15.4							○										
20.3	○	○	○	●	●	●	●	■									
20.4									●								
25.3	○	○	○	●	●	●	●	■	●								
25.4										●							
30.3	○	○	○	●	●	●	●		●	●							
30.4											●						
32.3								■									
40.3	○	○	○	●	●	●	●	■	●	●	●	■					
40.4													●				
50.3	○	○	○	●	●	●	●	■	●	●	●	■	●				
50.4														●			
60.3	○	○	○	●	●	●	●		●	●	●		●	●			
60.4															●		
63.3								■									
80.3	○	○	○	●	●	●	●	■	●	●	●	■	●	●	■		
80.4																■	
100.3	○	○	○	●	●	●	●	■	●	●	●	■	●	●	■	■	
100.4																	■
125.3				■	■	■	■	■	●	●	●	■	●	●	■	■	■
150.3				■	■	■	■	■	●	●	●	■	●	●	■	■	■
200.3				■	■	■	■	■	●	●	●	■	●	●	■	■	■

## Ordering Code (example):

Precision flat and square bar steel with machining allowance, DIN 59350	=	2923.2343.
Width B	20.3 mm =	020.
Thickness S	4.2 mm =	004.
Length L	500 mm =	0500
Order No	=	2923.2343. 020. 004. 0500