

符合DIN 59350带有加工余量的精密扁钢和精密方钢

2923.2436.



材料:

1.2436 / X 210 CrW 12

冷锻模钢

结构:


厚度已精磨, 宽度已打磨或铣削, 长度已加工

说明:

● = 适用于 500 mm 和 1000 mm 长度

○ = 仅适用于 500 mm 长度

■ = 仅适用于 1000 mm 长度



2923.2436. 符合DIN 59350带有加工余量的精密扁钢和精密方钢

| s | 2.2 | 3.2 | 4.2 | 5.2 | 6.2 | 8.2 | 10.4 | 12.4 | 15.4 | 20.4 | 25.4 | 30.4 | 40.4 | 50.4 |
|-------|-----|-----|-----|-----|-----|-----|------|------|------|------|------|------|------|------|
| b | | | | | | | | | | | | | | |
| 8.2 | | | | | | ○ | | | | | | | | |
| 10.3 | ○ | ● | ● | ● | ● | ● | | | | | | | | |
| 10.4 | | | | | | | ● | | | | | | | |
| 12.4 | | | | | | | | ● | | | | | | |
| 15.3 | ○ | ● | ● | ● | ● | ● | ● | ○ | | | | | | |
| 15.4 | | | | | | | | | ○ | | | | | |
| 20.3 | ○ | ● | ● | ● | ● | ● | ● | ● | ● | | | | | |
| 20.4 | | | | | | | | | | ● | | | | |
| 25.3 | ○ | ● | ● | ● | ● | ● | ● | ● | ● | ● | | | | |
| 25.4 | | | | | | | | | | | ● | | | |
| 30.3 | ○ | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | | | |
| 30.4 | | | | | | | | | | | | ● | | |
| 40.3 | ○ | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | | |
| 40.4 | | | | | | | | | | | | | ● | |
| 50.3 | ○ | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ○ | |
| 50.4 | | | | | | | | | | | | | | ■ |
| 60.3 | ○ | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ○ | |
| 80.3 | ○ | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | |
| 100.3 | ○ | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ● | ■ |
| 125.3 | ○ | ○ | ○ | ○ | ○ | ○ | ● | ● | ● | ● | ● | ● | ● | ■ |
| 150.3 | ○ | ○ | ○ | ○ | ○ | ○ | ● | ● | ● | ● | ● | ● | ● | ■ |
| 200.3 | ○ | ○ | ○ | ○ | ○ | ○ | ● | ● | ● | ● | ● | ● | ● | ■ |
| 250.3 | ○ | ○ | ○ | ○ | ○ | ○ | ● | ● | ● | ● | ● | ● | ● | ■ |
| 300.3 | ○ | ○ | ○ | ○ | ○ | ○ | ● | ● | ● | ● | ● | ● | ○ | |

订购示例:

符合DIN 59350带有加工余量的精密扁钢和精密方钢 = 2923.2436.

宽 B 25.3 mm = 025.

厚度 S 2.2 mm = 002.

长度 L 500 mm = 0500

订购编号 = 2923.2436. 025. 002. 0500