






# KLUZNÁ DESKA, BRONZOVÉ S MAZACÍ DRÁŽKOU, CNOMO



2960.54.45.



2960.54.45.



## Materiál:

Bronz

## Upozornění:

Dodává se bez šroubů.

## Upevnění:

Použít šrouby s válcovou hlavou  
DIN EN ISO 4762 M10.

## 2960.54.45. Kluzná deska, bronzové s mazací drážkou, CNOMO

Objednací číslo	Tvar	b	a	e	e <sub>1</sub>	e <sub>2</sub>	e <sub>3</sub>	e <sub>4</sub>	e <sub>5</sub>	e <sub>6</sub>	e <sub>7</sub>	e <sub>8</sub>	e <sub>9</sub>	Počet otvorů
2960.54.45.070.100	A	70	100	20	-	-	-	70	-	-	-	-	10	2
2960.54.45.070.150	B	70	150	10	20	-	-	70	120	-	-	-	10	3
2960.54.45.150.150	H	150	150	25	75	100	45	95	120	-	-	-	50	4
2960.54.45.100.100	I	100	100	30	50	-	-	45	70	-	-	-	25	3