






PŁYTKA ŚLIZGOWA, Z ROWKIEM SMAROWYM (BRĄZ), CNOMO



2960.54.45.



2960.54.45.



Material:

Brąz

Uwaga:

Śruby nie wchodzą w zakres dostawy.

Mocowanie:

Stosować śruby z łbem walcowym

DIN EN ISO 4762 M10.

2960.54.45. Płytką ślizgowa, z rowkiem smarowym (brąz), CNOMO

| Numer katalogowy | Typ | b | a | e | e ₁ | e ₂ | e ₃ | e ₄ | e ₅ | e ₆ | e ₇ | e ₈ | e ₉ | Liczba otworów |
|--------------------|-----|-----|-----|----|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| 2960.54.45.070.100 | A | 70 | 100 | 20 | - | - | - | 70 | - | - | - | - | 10 | 2 |
| 2960.54.45.070.150 | B | 70 | 150 | 10 | 20 | - | - | 70 | 120 | - | - | - | 10 | 3 |
| 2960.54.45.150.150 | H | 150 | 150 | 25 | 75 | 100 | 45 | 95 | 120 | - | - | - | 50 | 4 |
| 2960.54.45.100.100 | I | 100 | 100 | 30 | 50 | - | - | 45 | 70 | - | - | - | 25 | 3 |