



VODÍČÍ DESKA, BRONZOVÁ S GRAFITOVÝMI TĚLÍSKY, VDI 3357

2960.89.



2960.89.



2960.89. Vodíčí deska, Bronzová s grafitovými tělísky, VDI 3357

Objednací číslo	Tvar	b	a	l ₁	l ₂	e	e ₁	d	d ₁	f	c	t	r	Počet otvorů
2960.89.063.180	A	63	180	20	90	50	36	14	20	18	36	16	16	3
2960.89.063.200	A	63	200	20	90	50	36	14	20	18	36	16	16	3
2960.89.063.224	A	63	224	20	90	50	36	14	20	18	36	16	16	3
2960.89.071.180	A	71	180	20	90	50	36	14	20	18	36	16	16	3
2960.89.071.200	A	71	200	20	90	50	36	14	20	18	36	16	16	3
2960.89.071.224	A	71	224	20	90	50	36	14	20	18	36	16	16	3
2960.89.090.200	A	90	200	20	100	50	50	18	26	28	45	21	25	3
2960.89.090.224	A	90	224	20	100	50	50	18	26	28	45	21	25	3
2960.89.090.250	A	90	250	20	100	50	50	18	26	28	45	21	25	3
2960.89.112.200	A	112	200	20	100	50	50	18	26	28	45	21	25	3
2960.89.112.224	A	112	224	20	100	50	50	18	26	28	45	21	25	3
2960.89.112.250	A	112	250	20	100	50	50	18	26	28	45	21	25	3
2960.89.140.315	B	140	315	40	150	80	90	22	33	36	45	25,5	31,5	4
2960.89.190.400	B	190	400	40	150	80	90	22	33	36	56	25,5	31,5	4
2960.89.240.500	B	240	500	40	250	160	160	26	40	36	56	30,5	31,5	4
2960.89.240.630	B	240	630	40	250	160	160	26	40	36	56	30,5	31,5	4

Materiál:

Bronz s grafitovými tělísky, nenáročný na údržbu

Upozornění:

Dodává se bez šroubů.

Upevnění:

Použit šrouby s válcovou hlavou DIN EN ISO 4762.