


drylin®-Disk, aus iglidur® J



Bestellschlüssel

JDRM-4209TR10x2




Abmessungen [mm]

Bestellnummer	Flächentrag- anteil [mm²]	d3	d4	d5	b1	Gewinde d1 x P	max. stat. F axial*	
		h9					[N]	
JDRM-4209TR10x2	Neu!	127	42	34	5	9	TR10x2	508
JDRM-4811TR12x3	Neu!	181	48	38	6	11	TR12x3	724
JDRM-4811TR14x4	Neu!	207	48	38	6	11	TR14x4	828
JDRM-4811TR16x4	Neu!	241	48	38	6	11	TR16x4	964
JDRM-4811TR18x4	Neu!	276	48	38	6	11	TR18x4	1.104
JDRM-5513TR20x4	Neu!	367	55	45	7	13	TR20x4	1.468
JDRM-5513TR24x5	Neu!	439	55	45	7	13	TR24x5	1.756
JDRM-6214TR30x6	Neu!	551	62	50	7	13	TR30x6	2.204
JDRM-7016TR36x6	Neu!	829	70	58	7	16	TR36x6	3.316

* max. stat. F axial kann bei Verwendung mit Flanschmutter auf addiert werden

Notizen



Lieferzeit ab Lager



Preise Online-Preisliste
www.igus.de/de/jdrm