



drylin®-Gewindetribe | Lieferprogramm

Flansch-Trapezgewindemuttern, aus iglidur® W300, Linksgewinde



Bestellschlüssel

WFLM-2525TR10x2



Abmessungen [mm]

Bestellnummer	Flächentrag- anteil [mm²]	d2 h9	d3	d4	d5	b1	b2	Gewinde d1 x P	max. stat. F axial [N]
WFLM-2525TR10x2	352	25	42	34	5	25	10	TR10x2	1.760
WFLM-2835TR12x3	576	28	48	38	6	35	12	TR12x3	2.880
WFLM-2835TR14x4	658	28	48	38	6	35	12	TR14x4	3.290
WFLM-2835TR16x2	822	28	48	38	6	35	12	TR16x2	4.110
WFLM-2835TR16x4	768	28	48	38	6	35	12	TR16x4	3.840
WFLM-2835TR18x4	878	28	48	38	6	35	12	TR18x4	4.390
WFLM-3244TR20x4	1.242	32	55	45	7	44	12	TR20x4	6.210
WFLM-3244TR24x5	1.484	32	55	45	7	44	12	TR24x5	7.420
WFLM-3846TR26x5	1.696	38	62	50	7	46	14	TR26x5	7.900*
WFLM-3846TR28x5	1.840	38	62	50	7	46	14	TR28x5	5.900*
WFLM-3846TR30x6	1.948	38	62	50	7	46	14	TR30x6	4.470*

* reduzierte Axiallast aufgrund der Muttergeometrie



Lieferzeit ab Lager

Preise Online-Preisliste
www.igus.de/de/wflm