



Flansch-Steilgewindemuttern, aus iglidur® J
iglidur® J – bester Verschleiß im Trockenlauf



Bestellschlüssel

JFRM-2020SG8x10



Rechtsgewinde – Abmessungen [mm]

Bestellnummer	Flächentrag- anteil [mm²]	d2	d3	d4	d5	b1	b2	Gewinde d1 x P	max. stat. Last [N]
JFRM-1315SG6,35x12,7	107	13	25	19	3	15	5	SG6,35x12,7	100*
JFRM-2020SG8x10	232	20	34	28	4	20	5	SG8x10	458*
JFRM-2020SG8x15	183	20	34	28	4	20	5	SG8x15	458
JFRM-2525SG10x12	324	25	42	34	5	25	10	SG10x12	810
JFRM-2525SG10x50	177	25	42	34	5	25	10	SG10x50	443
JFRM-2835SG12x25	337	28	48	38	6	35	12	SG12x25	843
JFRM-2835SG18x24	945	28	48	38	6	35	12	SG18x24	2.363
JFRM-2835SG18x100	500	28	48	38	6	35	12	SG18x100	1.250

Linksgewinde – Abmessungen [mm]

Bestellnummer	Flächentrag- anteil [mm²]	d2	d3	d4	d5	b1	b2	Gewinde d1 x P	max. stat. Last [N]
JFLM-2525SG10x12	324	25	42	34	5	25	10	SG10x12	810
JFLM-2525SG10x50	177	25	42	34	5	25	10	SG10x50	443
JFLM-2835SG12x25	337	28	48	38	6	35	12	SG12x25	843
JFLM-2835SG18x24	945	28	48	38	6	35	12	SG18x24	2.363
JFLM-2835SG18x100	500	28	48	38	6	35	12	SG18x100	1.250

* reduzierte Last aufgrund der Muttergeometrie

Andere Gewindegrößen, Muttergeometrien und höhere Lasten auf Anfrage




Lieferzeit ab Lager



Preise Online-Preisliste
www.igus.de/de/jfrm-sg
www.igus.de/de/jflm-sg

Zero-Backlash-Gewindemuttern, aus iglidur® J
iglidur® J – bester Verschleiß im Trockenlauf



Bestellschlüssel

JFRM-ZB-0001-HH08x10



Abmessungen [mm]

Bestellnummer	d1	d2	d3	d4	d5	b1*	b2	Gewinde d1 x P
JFRM-ZB-0001-HH6,35x12,7	6,35	13,5	28	22,2	3,7	31-35	4,1	SG6,35x12,7
JFRM-ZB-0001-HH08x10	8	20	38,1	28,3	5,2	41-47	4,8	SG8x10
JFRM-ZB-0001-HH08x15	8	20	38,1	28,3	5,2	41-47	4,8	SG8x15
JFRM-ZB-0001-HH10x12	10	20	38,1	28,3	5,2	41-47	4,8	SG10x12
JFRM-ZB-0001-HH10x50	10	20	38,1	28,3	5,2	41-47	4,8	SG10x50

* variabel je nach Gewindesteigung / Spiel

Sondergrößen auf Anfrage

Kombinierbar mit Steilgewindespindeln ► Seite 1092



Lieferzeit ab Lager



Preise Online-Preisliste
www.igus.de/de/jfrm-zb