

... Hybridlager klem men

Die Handklemmung für drylin® W-Hybridlager

Eine integrierte, schnelle und einfache Klemmfunktion war der Wunsch vieler Anwender der drylin® W-Hybridlager, den wir gerne erfüllen. Mit der neuen Handklemmung können die drylin® W-Hybridlager an gewünschter Stelle positioniert und geklemmt werden. Die Klemmung ist in Baugröße 10 verfügbar und einsetzbar auf drylin® W-Einzel- und Doppelwellenprofile.

- Einfache und effiziente Klemmung per Reibschluß
- Optimierte Kraftaufnahme durch Doppelrollenlager
- Schmierfrei gleitgelagerte Kunststoffrollen
- Geringe Verschiebekräfte durch Prinzip "Rollen & gleiten"
- Sehr leiser Lauf

Typische Anwendungsbereiche:

Manuelle Verstellungen von Türen und Bedienpanels


Manual clamp for drylin® W-hybrid bearings

An integrated, quick and easy clamping function was the wish of many users of drylin® W hybrid bearings, which we would be happy to fulfil. With the new manual clamping the drylin® W hybrid bearings can be positioned at the required place and clamped. The clamp is available in size 10 and can be used on drylin® W single and double shaft profile.

- Simple and efficient clamping by friction locking
- Optimised forces absorption by double roller bearing
- Lubricant free bearing-supported plastic roller
- Combined sliding and rolling for low displacement forces
- Extremely quiet operation

Typical application areas:

Manual adjustment of doors and control panel units



Abmessungen Dimensions [mm]

Bestellnr. Part No.	Gewicht [g]	A1	A3	B	C1	C3	G1	H	K2 für Schraube for screw	Kz max.
WJRM-21-10-HKA	115	16,5	6,5	31	35	22	27	28	M6	25
WJRM-21-16-HKA	250	25	9	44	48	30	32	41	M8	25
WJRM-21-20-HKA	320	30	9	52	52	34	38	49	M8	25



Lieferbar Available
ab Lager from stock



www.igus.de/drylinWJRM-HKA
www.igus.eu/drylinWJRM-HKA