


For new constructions:
Series B15 "E2 mini"
▶ page 5.54

Series B15 classic E2 mini

igus® E-ChainSystems®





- 1 Mounting bracket with integrated strain relief
- 2 Dirt-repellent, contoured exterior
- 3 Interior separation with Vertical separators possible
- 4 Small pitch for low-noise, smooth operation
- 5 Snap-open along outer radius with film-hinge

● ● ● Price index




Phone +49- (0) 22 03-96 49-800
Fax +49- (0) 22 03-96 49-222

igus® GmbH
51147 Cologne



Unsupported length

FL_G = with straight upper run
 FL_B = with permitted sag



B15 classic - snap-open along inner radius


Part No.	B_i [mm]	B_a [mm]	R [mm] Bending Radii
B15.1.□.0	15	26	038 048 075
B15.2.□.0	25	36	110 125 145
B15.3.□.0	38	49	180
B15.4.□.0	50	61	180

Radii for all widths!

*available upon request!

Supplement Part No. with required radius. Example: **B15.2.048.0**
Bending radii listed above can be combined with every chain width!

Part No. structure



- Order example 2,0 m complete E-Chain®**
(indicate chain-lengths or number of links)
- 2,0 m (66 links) **Series B15.2.048.0**
 - + 2 separators **152** assembled each 2nd link
 - + 1 set mounting brackets + tiwrap plates **102.12PZ**