





Steel mounting bracket

- Locked connection to E-Tube
- Electrically conductive
- Minimized external width

Moving end (outer link)
482...1



Possible installation conditions -
Further installation angles ► installation sketch

482...2

Fixed end (inner link)


Dimensions and order configurations

482...1

Moving end


482...2

Fixed end



Part No. structure

482.	050.	12	A1
------	------	----	----



Full set, for both ends:

482.050.12

Single-part order:

482.050.1

Mounting bracket with bore

482.050.2

Mounting bracket with pin

For Series	Part No. full set	Dim. A [mm]
48.025. ►	482.025.12	-
48.050. ►	482.050.12	22
48.075. ►	482.075.12	47
48.100. ►	482.100.12	72
48.130. ►	482.130.12	102

Please add the Part No. with the requested index - e.g. 482.050.12

For the preassembled mode please add the index A1 ... A4 e.g. 482.050.12 A1

The following parts are required for attachment of the mounting brackets:

- Socket head cap bolt M5 DIN 912-8.8 Length depends on the thickness of the attachment base
- Washer 5,3 DIN 125-ST ● Hexagon nut M5 DIN 934-8

Phone +49- (0) 22 03-96 49-800
Fax +49- (0) 22 03-96 49-222

igus GmbH
51147 Cologne

Internet: www.igus.eu
E-mail: info@igus.de

