


Series E300 - split crossbar along the outer radius

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
E300.075. <input type="text"/> .0	75	95	<input type="text"/> 075	<input type="text"/> 100 <input type="text"/> 125 <input type="text"/> 150 <input type="text"/> 200 <input type="text"/> 250 <input type="text"/> 300	≈ 1,60

Ba: pin dimension approx. 0,3 - 0,5 mm wider!

Supplement Part No. with required radius. Example: E300.075.  100 .0

0 = standard color, other colors ▶ page 1.39 · Pitch = 67 mm/link - Links/m = 15




Series E300 - split crossbar along the outer radius with 2-chamber system

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
E300.2/45. <input type="text"/> .0	48/48	120	<input type="text"/> 075	<input type="text"/> 100 <input type="text"/> 125 <input type="text"/> 150 <input type="text"/> 200 <input type="text"/> 250 <input type="text"/> 300	≈ 1,78

Ba: pin dimension approx. 0,3 - 0,5 mm wider!

Supplement Part No. with required radius. Example: E300.2/45.  100 .0

0 = standard color, other colors ▶ page 1.39 · Pitch = 67 mm/link - Links/m = 15




Series E300 - split crossbar along the outer radius with 3-chamber system

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
E300.3/45. <input type="text"/> .0	47/46/47	170	<input type="text"/> 075	<input type="text"/> 100 <input type="text"/> 125 <input type="text"/> 150 <input type="text"/> 200 <input type="text"/> 250 <input type="text"/> 300	≈ 1,92

Ba: pin dimension approx. 0,3 - 0,5 mm wider!

Supplement Part No. with required radius. Example: E300.3/45.  100 .0

0 = standard color, other colors ▶ page 1.39 · Pitch = 1 m = 15 Links



Part No. structure

E300.075.  100. 0

