


Option 1: Vertical Separators

Vertical Separators are used if a vertical subdivision of the E-Chain® interior is required -

By standard Vertical Separators are assembled every other E-Chain® link

- **Standard** subdivision with Vertical Separator 311


(if you select bending radius R = 100 please use Vertical Separator 34511)



Vertical Separator*


unassembled	301
assembled	311

*not suitable for bending radius = 100



Vertical Separator, for bending radius R = 100

unassembled	34501
assembled	34511




Option 2: Full-Width Shelves

For applications involving many thin cables with similar or identical diameters


- Vertical Separator, slotted 312 or Vertical Separator, slotted 312.24 with wide base

can be combined with Full-Width Shelf 221.X




Vert. Separator, slotted

unassembled	302
assembled	312



Vert. Separator, slotted


unassembled	302.24
assembled	312.24



Width X [mm]	Part No. unassembled	Part No. assembled
50	320.050	321.050
75	320.075	321.075
100	320.100	321.100
115	320.115	321.115
125	320.125	321.125

Width X [mm]	Part No. unassembled	Part No. assembled
150	320.150	321.150
175	320.175	321.175
200	320.200	321.200
225	320.225	321.225
250	320.250	321.250


Full-Width Shelf



Option 3: Shelves


For applications involving many cables with similar or identical diameters. Partial separation into individual chambers can be achieved and the entire width Bi-10 mm can be used

- Shelf 2210.X can be combined with Side Plate 313 and Middle Plate 314
- Option 3 "Shelves" can also be combined with option 1 "Vertical Separators"




Side Plate

unassembled	303
assembled	313



Middle Plate


unassembled	304
assembled	314



Width X [mm]	Part No. unassembled	Part No. assembled
018	2200.18	2210.18
023	2200.23	2210.23
028	2200.28	2210.28
033	2200.33	2210.33
038	2200.38	2210.38
043	2200.43	2210.43
048	2200.48	2210.48

Width X [mm]	Part No. unassembled	Part No. assembled
058	2200.58	2210.58
068	2200.68	2210.68
073	2200.73	2210.73
088	2200.88	2210.88
099	2200.99	2210.99
124	2200.124	2210.124
149	2200.149	2210.149

Shelf



E2 E-Tubes Type R
Inner height: 45 mm

Phone +49- (0) 22 03-96 49-800
Fax +49- (0) 22 03-96 49-222

