




Series B17 - snap-open along outer radius

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii	Weight [kg/m]
B17.1. <input type="text"/> .0	15	25,5	048	063 075 100 125	≈ 0,52
B17.2. <input type="text"/> .0	25	35,5	048	063 075 100 125	≈ 0,59
B17.3. <input type="text"/> .0	38	48,5	048	063 075 100 125	≈ 0,65
B17.4. <input type="text"/> .0	50	60,5	048	063 075 100 125	≈ 0,70
B17.5. <input type="text"/> .0	63	76,0	063	075 100 125	≈ 0,83
B17.6. <input type="text"/> .0	80	93,0	048	063 075 100 125	≈ 0,92
B17.7. <input type="text"/> .0	100	113,0	063	075 100 125	≈ 1,06

Supplement Part No. with required radius. Example: B17.1.  .0

0 = standard color, other colors ► page 1.39 · Pitch = 30,5 mm/link - Links/m = 33

Part No. structure



Series B17i - snap-open along inner radius

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii	Weight [kg/m]
B17i.1. <input type="text"/> .0	15	25,5	048	063 075 100 125	≈ 0,52
B17i.2. <input type="text"/> .0	25	35,5	048	063 075 100 125	≈ 0,59
B17i.3. <input type="text"/> .0	38	48,5	048	063 075 100 125	≈ 0,65
B17i.4. <input type="text"/> .0	50	60,5	048	063 075 100 125	≈ 0,70
B17i.5. <input type="text"/> .0	63	76,0	063	075 100 125	≈ 0,83
B17i.6. <input type="text"/> .0	80	93,0	048	063 075 100 125	≈ 0,92
B17i.7. <input type="text"/> .0	100	113,0	063	075 100 125	≈ 1,06

The widths  $B_i$  15/25/50/63/80/100 are available upon request. Time of delivery approx. 6-8 weeks after order.

Supplement Part No. with required radius. Example: B17i.3.  .0

0 = standard color, other colors ► page 1.39 · Pitch = 30,5 mm/link - Links/m = 33

Part No. structure

