


Option 1: Vertical Separators

Vertical Separators are used if a vertical subdivision of the E-Chain® interior is required -

By standard Vertical Separators are assembled every other E-Chain® link

- **Standard** subdivision with Vertical Separator 1686.01
- **Strain Relief Separator 1686.01.Z**, integrable in the mounting bracket, to position at any point - can be combined with Full-Width Shelf 321.X and Shelf 2210.X




Vertical Separator

unassembled	1685.01
assembled	1686.01



Strain Relief Separator

unassembled	1685.01.Z
assembled	1686.01.Z




E2 E-Tubes Type R
Inner height: 50 mm

Option 2: Full-Width Shelves


For applications involving many thin cables with similar or identical diameters

- Vertical Separator, slotted 1686.02 for applications with Full-Width Shelf 321.X



Vert. Separator, slotted

unassembled	1685.02
assembled	1686.02




Phone +49- (0) 22 03-96 49-800
Fax +49- (0) 22 03-96 49-222

Width X [mm]	Part No. unassembled	Part No. assembled
050	320.050	321.050
075	320.075	321.075
100	320.100	321.100
115	320.115	321.115
125	320.125	321.125

Width X [mm]	Part No. unassembled	Part No. assembled
150	320.150	321.150
175	320.175	321.175
200	320.200	321.200
225	320.225	321.225
250	320.250	321.250


Full-Width Shelf



Option 3: Shelves


For applications involving many cables with similar or identical diameters. Partial separation into individual chambers can be achieved and the entire width Bi-10 mm can be used

- Shelf 2210.X can be combined with Middle Plate 1686.03 and Side Plate 1686.04




Middle Plate

unassembled	1685.03
assembled	1686.03



Side Plate

unassembled	1685.04
assembled	1686.04



Width X [mm]	Part No. unassembled	Part No. assembled
018	2200.18	2210.18
023	2200.23	2210.23
028	2200.28	2210.28
033	2200.33	2210.33
038	2200.38	2210.38
043	2200.43	2210.43
048	2200.48	2210.48

Width X [mm]	Part No. unassembled	Part No. assembled
058	2200.58	2210.58
068	2200.68	2210.68
073	2200.73	2210.73
088	2200.88	2210.88
099	2200.99	2210.99
124	2200.0124	2210.124
149	2200.0149	2210.149

Shelf

