




### The Standard - Option KMA\* - pivoting

- Recommended for unsupported and gliding applications
- Confined installation conditions
- Option - integrated C-profile strain relief device with Chainfix clip or strain relief tiwrap plates
- Corrosion resistant
- Universal mountable with attachment capability on all sides

\*KMA = Polymer Metal Mounting Bracket



The attachment variants arising automatically by the choice of the KMA mounting bracket




### Option KMA - locking


- Recommended for vertical hanging / standing applications

**Additionally:**

- Universal mountable
- C-profile option
- Corrosion resistant
- Locked connections
- At very high acceleration



The attachment variants arising automatically by the choice of the KMA mounting bracket




**Fixed end**

2800/7700... □.1 (pivoting)  
2900/7750... □.1 (locking)

**Moving end**

(pivoting) 2800/7700... □.2  
(locking) 2900/7750... □.2




Width index	Part No. full set pivoting	Part No. full set locking	C-profile option [mm]	Width index	Part No. full set pivoting	Part No. full set locking	C-profile option [mm]
.05.	2800/7700	2900/7750	.05. □.12. □ C 50	.23.	2800	2900	.23. □.12. □ C 225
.06.	2800	2900	.06. □.12. □ C 68	.237.	2800	2900	.237. □.12. □ C 237
.07.	2800/7700	2900/7750	.07. □.12. □ C 75	.25.	2800/7700	2900/7750	.25. □.12. □ C 250
.087.	2800	2900	.087. □.12. □ C 87	.262.	2800	2900	.262. □.12. □ C 262
.10.	2800/7700	2900/7750	.10. □.12. □ C 100	.28.	2800	2900	.28. □.12. □ C 275
.11.	2800/7700	2900/7750	.11. □.12. □ C 108	.29.	2800	2900	.29. □.12. □ C 287
.112.	2800	2900	.112. □.12. □ C 112	.30.	2800/7700	2900/7750	.30. □.12. □ C 300
.12.	2800/7700	2900/7750	.12. □.12. □ C 125	.312.	2800	2900	.312. □.12. □ C 312
.137.	2800	2900	.137. □.12. □ C 137	.325.	2800	2900	.325. □.12. □ C 325
.15.	2800/7700	2900/7750	.15. □.12. □ C 150	.337.	2800	2900	.337. □.12. □ C 337
.162.	2800	2900	.162. □.12. □ C 162	.350.	2800	2900	.350. □.12. □ C 350
.17.	2800/7700	2900/7750	.17. □.12. □ C 168	.362.	2800	2900	.362. □.12. □ C 362
.18.	2800	2900	.18. □.12. □ C 175	.375.	2800	2900	.375. □.12. □ C 375
.187.	2800	2900	.187. □.12. □ C 187	.387.	2800	2900	.387. □.12. □ C 387
.20.	2800/7700	2900/7750	.20. □.12. □ C 200	.400.	2800	2900	.400. □.12. □ C 400
.212.	2800	2900	.212. □.12. □ C 212				


Please insert **1** for odd number of links or **2** for even number of links

### Dimensions and order configurations

**Part No. structure (pivoting)**



**Part No. structure (locking)**



**Note:** The E4/00 System may end with either an inner side or an outer side link. Keep in mind that an outer side link always forms the first chain link at the moving end. The Part No. depends on an even or odd numbers of links. Please insert: **1** for odd number of links or **2** for even number of links

**Full set, for both ends:**

2900. 05. 2. 12. □ C (even)

**Single-part order:**

2900. 05. 2. 2. □ C (even)

Mounting bracket moving end

2900. 05. 2. 1. □ C (even)

Mounting bracket fixed end

