


Part No. structure



Series E03 - split crossbar along the outer radius

Part No.	<i>Bi</i> [mm]	<i>Ba</i> [mm]	<i>R</i> [mm]	Bending radii					Weight [kg/m]
E03.05. <input type="text"/> .0	5	8,7	<input type="text" value="010"/>	<input type="text" value="012"/>	<input type="text" value="015"/>	<input type="text" value="018"/>	<input type="text" value="028"/>	≈ 0,03	
E03.07. <input type="text"/> .0	7	10,7	<input type="text" value="010"/>	<input type="text" value="012"/>	<input type="text" value="015"/>	<input type="text" value="018"/>	<input type="text" value="028"/>	≈ 0,04	
E03.10. <input type="text"/> .0	10	13,7	<input type="text" value="010"/>	<input type="text" value="012"/>	<input type="text" value="015"/>	<input type="text" value="018"/>	<input type="text" value="028"/>	≈ 0,05	

Ba: pin dimension approx. 0,1 - 0,3 mm wider!

Supplement Part No. with required radius. Example: E03.05. .0

0 = standard color, other colors ► page 1.39 · Pitch = 10 mm/link - Links/m = 100

