


Easy Chain® | Series E200 · Z200 | Product Range



Series E200 - split crossbar along the outer radius

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
E200.05.□.0	57	74,4	055 075 100 150 200		≈ 0,70

Ba: pin dimension approx. 0,1 - 0,3 mm wider!

Supplement Part No. with required radius. Example: E200.05.100.0

0 = standard color, other colors ► page 1.39 · Pitch = 46 mm/link - Links/m = 22



Series E200 - split crossbar along the outer radius with 2-chamber system

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
E200.2/35.□.0	37	94,4	055 075 100 150 200		≈ 0,79
E200.2/50.□.0	50	120,4	055 075 100 150 200		≈ 0,82

Ba: pin dimension approx. 0,1 - 0,3 mm wider!

Supplement Part No. with required radius. Example: E200.2/50.100.0

0 = standard color, other colors ► page 1.39 · Pitch = 46 mm/link - Links/m = 22



Series Z200 - split crossbar along the inner radius

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
Z200.05.□.0	57	74,4	055 075 100 150 200		≈ 0,70

Ba: pin dimension approx. 0,1 - 0,3 mm wider!

Supplement Part No. with required radius. Example: Z200.05.100.0

0 = standard color, other colors ► page 1.39 · Pitch = 46 mm/link - Links/m = 22

Series Z200 - split crossbar along the inner radius with 2-chamber system

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
Z200.2/35.□.0	37	94,4	055 075 100 150 200		≈ 0,79
Z200.2/50.□.0	50	120,4	055 075 100 150 200		≈ 0,82

Ba: pin dimension approx. 0,1 - 0,3 mm wider!

Supplement Part No. with required radius. Example: Z200.2/50.100.0

0 = standard color, other colors ► page 1.39 · Pitch = 46 mm/link - Links/m = 22

