


Part No. structure



Series R07 E-Tube - zip-open along the outer radius

Part No.	<i>Bi</i> [mm]	<i>Ba</i> [mm]	<i>R</i> [mm]	Bending Radii	Weight [kg/m]
R07.10.□.0	10	16,5	038	048	≈ 0,14
R07.16.□.0	16	22,5	038	048	≈ 0,16
R07.20.□.0	20	27,0	038	048	≈ 0,17
R07.30.□.0	30	37,0	038	048	≈ 0,20
R07.40.□.0	40	47,0	038	048	≈ 0,23
R07.50.□.0	50	57,0	038	048	≈ 0,26

Supplement part no. with required radius (*R*) Example: R07.20.038.0

0 = standard color, other colors ▶ page 1.39 · Pitch = 20 mm/link - Links/m = 50



Phone +49- (0) 22 03-96 49-800
 Fax +49- (0) 22 03-96 49-222

igus® GmbH
 51147 Cologne

Internet: www.igus.eu
 E-mail: info@igus.de