

d1	d2	b1	d3	b2	d1 ³⁾		Housing bore		Shaft size		Part No.
					Max.	Min.	Max.	Min.	Max.	Min.	
3/4	7/8	1/2	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	A500FI-1214-08
3/4	7/8	3/4	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	A500FI-1214-12
3/4	7/8	1	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	A500FI-1214-16
7/8	1	1/2	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	A500FI-1416-08
7/8	1	3/4	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	A500FI-1416-12
7/8	1	1	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	A500FI-1416-16
1	1 1/8	1/2	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	A500FI-1618-08
1	1 1/8	3/4	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	A500FI-1618-12
1	1 1/8	1	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	A500FI-1618-16
1 1/4	1 13/32	1	1.6870	.0780	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	A500FI-2022-16
1 1/4	1 13/32	1 1/4	1.6870	.0780	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	A500FI-2022-20
1 1/2	1 21/32	1	2.0000	.0780	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	A500FI-2426-16
1 1/2	1 21/32	1 1/2	2.0000	.0780	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	A500FI-2426-24
1 3/4	1 15/16	2	2.3750	.0930	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	A500FI-2831-32
2	2 3/16	2	2.6250	.0930	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	A500FI-3235-32

iglidur® G Chapter ▶ Page 79

d1	d2	b1	d3	b2	d1 ³⁾		Housing bore		Shaft size		Part No.
					Max.	Min.	Max.	Min.	Max.	Min.	
1/8	3/16	1/8	.3120	.0320	.1269	.1251	.1878	.1873	.1243	.1236	GFI-0203-02
1/8	3/16	3/16	.3120	.0320	.1269	.1251	.1878	.1873	.1243	.1236	GFI-0203-03
1/8	3/16	1/4	.3120	.0320	.1269	.1251	.1878	.1873	.1243	.1236	GFI-0203-04
1/8	3/16	3/8	.3120	.0320	.1269	.1251	.1878	.1873	.1243	.1236	GFI-0203-06
3/16	1/4	1/4	.3750	.0320	.1892	.1873	.2503	.2497	.1865	.1858	GFI-0304-04
3/16	1/4	3/8	.3750	.0320	.1892	.1873	.2503	.2497	.1865	.1858	GFI-0304-06
3/16	1/4	1/2	.3750	.0320	.1892	.1873	.2503	.2497	.1865	.1858	GFI-0304-08
1/4	5/16	1/4	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	GFI-0405-04
1/4	5/16	5/16	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	GFI-0405-05
1/4	5/16	3/8	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	GFI-0405-06
1/4	5/16	1/2	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	GFI-0405-08
1/4	5/16	3/4	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	GFI-0405-12
5/16	3/8	1/4	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	GFI-0506-04
5/16	3/8	3/8	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	GFI-0506-06
5/16	3/8	1/2	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	GFI-0506-08
5/16	3/8	3/4	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	GFI-0506-12
3/8	15/32	1/4	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	GFI-0607-04
3/8	15/32	5/16	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	GFI-0607-05
3/8	15/32	3/8	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	GFI-0607-06
3/8	15/32	1/2	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	GFI-0607-08
3/8	15/32	3/4	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	GFI-0607-12
3/8	15/32	7/8	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	GFI-0607-14
7/16	17/32	1/4	.7500	.0460	.4406	.4379	.5316	.5309	.4365	.4355	GFI-0708-04
7/16	17/32	1/2	.7500	.0460	.4406	.4379	.5316	.5309	.4365	.4355	GFI-0708-08
1/2	19/32	1/4	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	GFI-0809-04
1/2	19/32	5/16	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	GFI-0809-05

³⁾ After press-fit. Testing methods ▶ Page 57

d1	d2	b1	d3	b2	d1 ³⁾		Housing bore		Shaft size		Part No.
					Max.	Min.	Max.	Min.	Max.	Min.	
1/2	19/32	3/8	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	GFI-0809-06
1/2	19/32	1/2	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	GFI-0809-08
1/2	19/32	3/4	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	GFI-0809-12
1/2	19/32	1	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	GFI-0809-16
5/8	23/32	3/8	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	GFI-1011-06
5/8	23/32	1/2	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	GFI-1011-08
5/8	23/32	3/4	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	GFI-1011-12
5/8	23/32	7/8	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	GFI-1011-14
5/8	23/32	1	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	GFI-1011-16
5/8	23/32	1 1/2	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	GFI-1011-24
3/4	7/8	1/8	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	GFI-1214-02
3/4	7/8	3/8	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	GFI-1214-06
3/4	7/8	1/2	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	GFI-1214-08
3/4	7/8	5/8	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	GFI-1214-10
3/4	7/8	3/4	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	GFI-1214-12
3/4	7/8	1 1/2	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	GFI-1214-16
3/4	7/8	1 1/2	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	GFI-1214-24
7/8	1	1/2	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	GFI-1416-08
7/8	1	3/4	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	GFI-1416-12
7/8	1	1	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	GFI-1416-16
7/8	1	1 1/4	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	GFI-1416-20
7/8	1	1 1/2	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	GFI-1416-24
1	1 1/8	1/2	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	GFI-1618-08
1	1 1/8	3/4	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	GFI-1618-12
1	1 1/8	1	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	GFI-1618-16
1	1 1/8	1 1/4	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	GFI-1618-20
1	1 1/8	1 1/2	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	GFI-1618-24
1 1/8	1 9/32	3/4	1.5620	.0780	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	GFI-1820-12
1 1/8	1 9/32	1 1/2	1.5620	.0780	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	GFI-1820-24
1 1/4	1 13/32	3/8	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	GFI-2022-06
1 1/4	1 13/32	3/4	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	GFI-2022-12
1 1/4	1 13/32	7/8	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	GFI-2022-14
1 1/4	1 13/32	1	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	GFI-2022-16
1 1/4	1 13/32	1 1/4	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	GFI-2022-20
1 1/4	1 13/32	1 1/2	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	GFI-2022-24
1 3/8	1 17/32	1	1.8750	.0780	1.3798	1.3758	1.5318	1.5308	1.3738	1.3722	GFI-2224-16
1 1/2	1 21/32	3/4	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	GFI-2426-12
1 1/2	1 21/32	1	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	GFI-2426-16
1 1/2	1 21/32	1 1/2	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	GFI-2426-24
1 3/4	1 15/16	1	2.3750	.0930	1.7547	1.7505	1.9381	1.9371	1.7487	1.7471	GFI-2831-16
1 3/4	1 15/16	1 1/2	2.3750	.0930	1.7547	1.7505	1.9381	1.9371	1.7487	1.7471	GFI-2831-24
1 3/4	1 15/16	2	2.3750	.0930	1.7547	1.7505	1.9381	1.9371	1.7487	1.7471	GFI-2831-32
2	2 3/16	1	2.6250	.0930	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	GFI-3235-16
2	2 3/16	1 1/2	2.6250	.0930	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	GFI-3235-24
2	2 3/16	2	2.6250	.0930	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	GFI-3235-32
2 1/4	2 7/16	2	2.7500	.0930	2.2577	2.2531	2.4377	2.4365	2.2507	2.2489	GFI-3639-32

³⁾ After press-fit. Testing methods ▶ Page 57

d1	d2	b1	d3	b2	d1 ³⁾		Housing bore		Shaft size		Part No.
					Max.	Min.	Max.	Min.	Max.	Min.	
2 1/2	2 11/16	2	3.1250	.0930	2.5082	2.5035	2.6881	2.6869	2.5000	2.4999	GFI-4043-32
2 3/4	2 15/16	2	3.3750	.0930	2.7570	2.7523	2.9370	2.9358	2.7500	2.7490	GFI-4447-32

iglidur® H1 Chapter ▶ Page 297

d1	d2	b1	d3	b2	d1 ³⁾		Housing bore		Shaft size		Part No.
					h13	-0.14	Max.	Min.	Max.	Min.	
1/8	3/16	3/16	.3120	.0320	.1266	.1247	.1878	.1873	.1243	.1236	H1FI-0203-03
3/16	1/4	1/4	.3750	.0320	.1888	.1869	.2503	.2497	.1865	.1858	H1FI-0304-04
1/4	5/16	3/8	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	H1FI-0405-06
1/4	5/16	1/2	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	H1FI-0405-08
5/16	3/8	1/4	.5620	.0320	.3143	.3120	.3753	.3747	.3115	.3106	H1FI-0506-04
5/16	3/8	3/8	.5620	.0320	.3143	.3120	.3753	.3747	.3115	.3106	H1FI-0506-06
5/16	3/8	1/2	.5620	.0320	.3143	.3120	.3753	.3747	.3115	.3106	H1FI-0506-08
3/8	15/32	1/4	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	H1FI-0607-04
3/8	15/32	3/8	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	H1FI-0607-06
3/8	15/32	1/2	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	H1FI-0607-08
3/8	15/32	3/4	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	H1FI-0607-12
7/16	17/32	1/2	.7500	.0460	.4399	.4371	.5316	.5309	.4365	.4355	H1FI-0708-08
1/2	19/32	1/4	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H1FI-0809-04
1/2	19/32	3/8	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H1FI-0809-06
1/2	19/32	1/2	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H1FI-0809-08
1/2	19/32	3/4	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H1FI-0809-12
1/2	19/32	1	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H1FI-0809-16
5/8	23/32	1/2	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	H1FI-1011-08
5/8	23/32	3/4	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	H1FI-1011-12
5/8	23/32	1	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	H1FI-1011-16
3/4	7/8	1/2	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	H1FI-1214-08
3/4	7/8	3/4	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	H1FI-1214-12
3/4	7/8	1	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	H1FI-1214-16
7/8	1	1/2	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	H1FI-1416-08
7/8	1	3/4	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	H1FI-1416-12
7/8	1	1	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	H1FI-1416-16
1	1 1/8	1/2	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	H1FI-1618-08
1	1 1/8	3/4	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	H1FI-1618-12
1	1 1/8	1	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	H1FI-1618-16
1 1/4	1 13/32	1	1.6870	.0780	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	H1FI-2022-16
1 1/4	1 13/32	1 1/4	1.6870	.0780	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	H1FI-2022-20
1 1/2	1 21/32	1	2.0000	.0780	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	H1FI-2426-16
1 1/2	1 21/32	1 1/2	2.0000	.0780	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	H1FI-2426-24
1 3/4	1 15/16	2	2.3750	.0930	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	H1FI-2831-32
2	2 3/16	2	2.6250	.0930	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	H1FI-3235-32

³⁾ After press-fit. Testing methods ▶ Page 57

iglidur® H370 Chapter ▶ Page 382

d1	d2	b1	d3	b2	d1 ³⁾		Housing bore		Shaft size		Part No.
					h13	-0.14	Max.	Min.	Max.	Min.	
1/8	3/16	3/16	.3120	.0320	.1266	.1247	.1878	.1873	.1243	.1236	H370FI-0203-03
3/16	1/4	1/4	.3750	.0320	.1888	.1869	.2503	.2497	.1865	.1858	H370FI-0304-04
1/4	5/16	1/4	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	H370FI-0405-04
1/4	5/16	3/8	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	H370FI-0405-06
1/4	5/16	1/2	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	H370FI-0405-08
5/16	3/8	1/4	.5620	.0320	.3143	.3120	.3753	.3747	.3115	.3106	H370FI-0506-04
5/16	3/8	3/8	.5620	.0320	.3143	.3120	.3753	.3747	.3115	.3106	H370FI-0506-06
5/16	3/8	1/2	.5620	.0320	.3143	.3120	.3753	.3747	.3115	.3106	H370FI-0506-08
3/8	15/32	1/4	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	H370FI-0607-04
3/8	15/32	3/8	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	H370FI-0607-06
3/8	15/32	1/2	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	H370FI-0607-08
3/8	15/32	3/4	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	H370FI-0607-12
7/16	17/32	1/2	.7500	.0460	.4399	.4371	.5316	.5309	.4365	.4355	H370FI-0708-08
1/2	19/32	1/4	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H370FI-0809-04
1/2	19/32	3/8	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H370FI-0809-06
1/2	19/32	1/2	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H370FI-0809-08
1/2	19/32	3/4	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H370FI-0809-12
1/2	19/32	1	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	H370FI-0809-16
5/8	23/32	1/2	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	H370FI-1011-08
5/8	23/32	3/4	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	H370FI-1011-12
5/8	23/32	1	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	H370FI-1011-16
3/4	7/8	1/2	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	H370FI-1214-08
3/4	7/8	3/4	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	H370FI-1214-12
3/4	7/8	1	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	H370FI-1214-16
7/8	1	1/2	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	H370FI-1416-08
7/8	1	3/4	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	H370FI-1416-12
7/8	1	1	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	H370FI-1416-16
1	1 1/8	1/2	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	H370FI-1618-08
1	1 1/8	3/4	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	H370FI-1618-12
1	1 1/8	1	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	H370FI-1618-16
1 1/4	1 13/32	1	1.6870	.0780	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	H370FI-2022-16
1 1/4	1 13/32	1 1/4	1.6870	.0780	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	H370FI-2022-20
1 1/2	1 21/32	1	2.0000	.0780	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	H370FI-2426-16
1 1/2	1 21/32	1 1/2	2.0000	.0780	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	H370FI-2426-24
1 3/4	1 15/16	2	2.3750	.0930	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	H370FI-2831-32
2	2 3/16	2	2.6250	.0930	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	H370FI-3235-32

³⁾ After press-fit. Testing methods ▶ Page 57



Dimensions thrust washer Abmessungen Anlaufscheiben [mm]


Part No. Art.-Nr.	d1	d2	s	d4 h13	d5
GTM-0825-015	8	25	1.5	-	-
GTM-1220-010	12	20	1	-	-
GTM-4060-035	40	60	3.5	-	-
JTM-0615-015	6	15	1.5	-	-
JTM-0815-015	8	15	1.5	-	-
JTM-0818-015	8	18	1.5	13	1.5
JTM-1018-010	10	18	1	-	-
JTM-2644-015	26	44	1.5	35	3
JTM-6290-020	62	90	2	-	-



Dimensions sleeve
Abmessungen zylindrisch [inch]


Part No. Art.-Nr.	d1	d1 tolerance d1-Toleranz	d2	b1 h13
A181SI-0406-06	1/4	+0.2539 +0.2516	3/8	3/8
GSI-1216-08	3/4	+0.7590 +0.7560	1	1/2
GSI-1620-55	1	+1.0092 +1.0062	1 1/4	55/16
GSI-1620-14	1	+1.0092 +1.0062	1 1/4	7/8
GSI-1620-44	1	+1.0092 +1.0062	1 1/4	11/4
GSI-2428-44	1 1/2	+1.5107 +1.5067	1 3/4	11/4
GSI-2428-20	1 1/2	+1.5107 +1.5067	1 3/4	1 1/4
GSI-5659-48	3 1/2	+3.5830 +3.5028	59/16	3
H1SI-0810-12	1/2	+0.5034 +0.5006	5/8	3/4

Part No. Art.-Nr.	d1	d1 tolerance d1-Toleranz	d2	b1 h13
JSI-1011-10	5/8	+0.6280 +0.6253	23/32	5/8
JSI-1011-14	5/8	+0.6280 +0.6253	23/32	7/8
JSI-1011-20	5/8	+0.6280 +0.6253	23/32	1 1/4
JSI-2226-32	1 3/8	+1.3809 +1.3770	1 5/8	2
Q2SI-4852-48	3	+3.0071 +3.0024	3 1/4	3
QSI-2428-16	1 1/2	+1.5059 +1.5020	1 3/4	1
QSI-2428-24	1 1/2	+1.5059 +1.5020	1 3/4	1
QSI-2428-40	1 1/2	+1.5059 +1.5020	1 3/4	5/2



Dimensions clips bearing
Abmessungen Clipslager [mm]

Part No. Art.-Nr.	d1	d2	d3	d4	s	b1
MCM-12-018	12.0	13.6	14.4	17.0	0.8	3.4



Dimensions split bearing
Abmessungen Schlitzlager [inch]

Part No. Art.-Nr.	d1	d2	b1	d3	b2
MYI-05-10	5/16	0.3744	5/8	1/2	0.0299



Dimensions with flange
Abmessungen mit Bund [inch]

Part No. Art.-Nr.	d1	d1 tolerance d1-Toleranz	d2	d3	b1 h13	b2
GFI-1012-08	5/8	+0.6297 +0.6270	3/4	1/2	1	0.062
GFI-1012-12	5/8	+0.6297 +0.6270	3/4	3/4	1	0.062
GFI-1012-16	5/8	+0.6297 +0.6270	3/4	1	1	0.062
GFI-1214-18	3/4	+0.7541 +0.7505	7/8	1 1/4	1.125	0.062
ZFI-0304-06	3/16	+0.1888 +0.1869	1/4	3/8	0.375	0.032

Calculate online Online berechenbar
www.igus.eu/iglidur-experte
www.igus.de/iglidur-expert

Available Lieferbar
 from stock ab Lager

www.igus.de/iglidur
www.igus.eu/iglidur

Calculate online Online berechenbar
www.igus.eu/iglidur-experte
www.igus.de/iglidur-expert

Available Lieferbar
 from stock ab Lager

www.igus.de/iglidur
www.igus.eu/iglidur