

iglidur® H370 Kapitel ▶ Seite 305

d1	d2	b1 h13	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
1/8	3/16	3/16	.1266	.1247	.1878	.1873	.1243	.1236	H370SI-0203-03
3/16	1/4	1/4	.1888	.1869	.2503	.2497	.1865	.1858	H370SI-0304-04
3/16	1/4	3/8	.1888	.1869	.2503	.2497	.1865	.1858	H370SI-0304-06
1/4	5/16	1/4	.2521	.2498	.3128	.3122	.2490	.2481	H370SI-0405-04
1/4	5/16	3/8	.2518	.2495	.3128	.3122	.2490	.2481	H370SI-0405-06
1/4	5/16	1/2	.2518	.2495	.3128	.3122	.2490	.2481	H370SI-0405-08
5/16	3/8	1/4	.3143	.3120	.3753	.3747	.3115	.3106	H370SI-0506-04
5/16	3/8	3/8	.3143	.3120	.3753	.3747	.3115	.3106	H370SI-0506-06
5/16	3/8	1/2	.3143	.3120	.3753	.3747	.3115	.3106	H370SI-0506-08
3/8	15/32	1/4	.3768	.3745	.4691	.4684	.3740	.3731	H370SI-0607-04
3/8	15/32	3/8	.3768	.3745	.4691	.4684	.3740	.3731	H370SI-0607-06
3/8	15/32	1/2	.3768	.3745	.4691	.4684	.3740	.3731	H370SI-0607-08
3/8	15/32	5/8	.3768	.3745	.4691	.4684	.3740	.3731	H370SI-0607-10
3/8	15/32	3/4	.3768	.3745	.4691	.4684	.3740	.3731	H370SI-0607-12
7/16	17/32	1/2	.4399	.4371	.5316	.5309	.4365	.4355	H370SI-0708-08
7/16	17/32	3/4	.4399	.4371	.5316	.5309	.4365	.4355	H370SI-0708-12
1/2	19/32	1/4	.5024	.4996	.5941	.5934	.4990	.4980	H370SI-0809-04
1/2	19/32	3/8	.5024	.4996	.5941	.5934	.4990	.4980	H370SI-0809-06
1/2	19/32	1/2	.5024	.4996	.5941	.5934	.4990	.4980	H370SI-0809-08
1/2	19/32	5/8	.5024	.4996	.5941	.5934	.4990	.4980	H370SI-0809-10
1/2	19/32	3/4	.5024	.4996	.5941	.5934	.4990	.4980	H370SI-0809-12
1/2	19/32	1	.5024	.4996	.5941	.5934	.4990	.4980	H370SI-0809-16
9/16	21/32	1/2	.5649	.5620	.6566	.6559	.5615	.5605	H370SI-0910-08
9/16	21/32	5/8	.5649	.5620	.6566	.6559	.5615	.5605	H370SI-0910-10
9/16	21/32	3/4	.5649	.5620	.6566	.6559	.5615	.5605	H370SI-0910-12
5/8	23/32	1/2	.6274	.6246	.7192	.7184	.6240	.6230	H370SI-1011-08
5/8	23/32	3/4	.6274	.6246	.7192	.7184	.6240	.6230	H370SI-1011-12
5/8	23/32	1	.6274	.6246	.7192	.7184	.6240	.6230	H370SI-1011-16
3/4	7/8	1/2	.7532	.7499	.8755	.8747	.7491	.7479	H370SI-1214-08
3/4	7/8	3/4	.7532	.7499	.8755	.8747	.7491	.7479	H370SI-1214-12
3/4	7/8	1	.7532	.7499	.8755	.8747	.7491	.7479	H370SI-1214-16
7/8	1	1/2	.8782	.8749	1.0005	.9997	.8741	.8729	H370SI-1416-08
7/8	1	3/4	.8782	.8749	1.0005	.9997	.8741	.8729	H370SI-1416-12
7/8	1	1	.8782	.8749	1.0005	.9997	.8741	.8729	H370SI-1416-16
1	1 1/8	1/2	1.0032	.9999	1.1255	1.1247	.9991	.9979	H370SI-1618-08
1	1 1/8	3/4	1.0032	.9999	1.1255	1.1247	.9991	.9979	H370SI-1618-12
1	1 1/8	1	1.0032	.9999	1.1255	1.1247	.9991	.9979	H370SI-1618-16
1 1/8	1 1/4	3/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	H370SI-1820-12
1 1/8	1 1/4	1	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	H370SI-1820-16
1 1/8	1 1/4	1 1/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	H370SI-1820-20
1 1/4	1 13/32	3/4	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	H370SI-2022-12
1 1/4	1 13/32	1	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	H370SI-2022-16
1 1/4	1 13/32	1 1/4	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	H370SI-2022-20
1 1/2	1 21/32	1	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	H370SI-2426-16

<sup>3)</sup> nach dem Einpressen. Messverfahren ▶ Seite 57

d1	d2	b1 h13	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
1 1/2	1 21/32	1 1/2	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	H370SI-2426-24
1 5/8	1 25/32	1	1.6287	1.6248	1.7818	1.7808	1.6238	1.6222	H370SI-2629-16
1 5/8	1 25/32	1 1/2	1.6287	1.6248	1.7818	1.7808	1.6238	1.6222	H370SI-2629-24
1 3/4	1 15/16	1	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	H370SI-2831-16
1 3/4	1 15/16	2	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	H370SI-2831-32
1 7/8	2 1/16	1	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	H370SI-3033-16
1 7/8	2 1/16	2	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	H370SI-3033-32
2	2 3/16	1	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	H370SI-3235-16
2	2 3/16	2	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	H370SI-3235-32

iglidur® J Kapitel ▶ Seite 141

d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
1/8	3/16	3/16	.1269	.1251	.1878	.1873	.1243	.1236	JSI-0203-03
1/8	1/4	1/4	.1280	.1262	.2515	.2510	.1250	.1241	JSI-0204-04
1/8	1/4	3/8	.1280	.1262	.2515	.2510	.1250	.1241	JSI-0204-06
3/16	1/4	1/4	.1892	.1873	.2503	.2497	.1865	.1858	JSI-0304-04
3/16	1/4	3/8	.1892	.1873	.2503	.2497	.1865	.1858	JSI-0304-06
3/16	1/4	1/2	.1892	.1873	.2503	.2497	.1865	.1858	JSI-0304-08
3/16	5/16	5/16	.1905	.1887	.3140	.3135	.1875	.1866	JSI-0305-05
3/16	5/16	3/8	.1905	.1887	.3140	.3135	.1875	.1866	JSI-0305-06
3/16	5/16	1/2	.1905	.1887	.3140	.3135	.1875	.1866	JSI-0305-08
1/4	5/16	1/4	.2521	.2498	.3128	.3122	.2490	.2481	JSI-0405-04
1/4	5/16	3/8	.2521	.2498	.3128	.3122	.2490	.2481	JSI-0405-06
1/4	5/16	1/2	.2521	.2498	.3128	.3122	.2490	.2481	JSI-0405-08
1/4	3/8	1/4	.2539	.2516	.3765	.3760	.2500	.2491	JSI-0406-04
1/4	3/8	1/2	.2539	.2516	.3765	.3760	.2500	.2491	JSI-0406-08
1/4	3/8	3/4	.2539	.2516	.3765	.3760	.2500	.2491	JSI-0406-12
1/4	3/8	1	.2539	.2516	.3765	.3760	.2500	.2491	JSI-0406-16
5/16	3/8	1/4	.3148	.3125	.3753	.3747	.3115	.3106	JSI-0506-04
5/16	3/8	3/8	.3148	.3125	.3753	.3747	.3115	.3106	JSI-0506-06
5/16	3/8	1/2	.3148	.3125	.3753	.3747	.3115	.3106	JSI-0506-08
5/16	3/8	3/4	.3148	.3125	.3753	.3747	.3115	.3106	JSI-0506-12
5/16	7/16	3/8	.3164	.3141	.4390	.4385	.3125	.3116	JSI-0507-06
5/16	7/16	1/2	.3164	.3141	.4390	.4385	.3125	.3116	JSI-0507-08
5/16	7/16	5/8	.3164	.3141	.4390	.4385	.3125	.3116	JSI-0507-10
3/8	15/32	1/4	.3773	.3750	.4691	.4684	.3740	.3731	JSI-0607-04
3/8	15/32	3/8	.3773	.3750	.4691	.4684	.3740	.3731	JSI-0607-06
3/8	15/32	1/2	.3773	.3750	.4691	.4684	.3740	.3731	JSI-0607-08
3/8	15/32	5/8	.3773	.3750	.4691	.4684	.3740	.3731	JSI-0607-10
3/8	15/32	3/4	.3773	.3750	.4691	.4684	.3740	.3731	JSI-0607-12
3/8	1/2	3/16	.3773	.3750	.4691	.4684	.3740	.3731	JSI-0608-03
3/8	1/2	3/8	.3773	.3750	.4691	.4684	.3740	.3731	JSI-0608-06
3/8	1/2	1/2	.3773	.3750	.4691	.4684	.3740	.3731	JSI-0608-08
3/8	1/2	5/8	.3773	.3750	.4691	.4684	.3740	.3731	JSI-0608-10

<sup>3)</sup> nach dem Einpressen. Messverfahren ▶ Seite 57

d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
7/16	17/32	1/2	.4406	.4379	.5316	.5309	.4365	.4355	<b>JSI-0708-08</b>
7/16	17/32	3/4	.4406	.4379	.5316	.5309	.4365	.4355	<b>JSI-0708-12</b>
1/2	19/32	1/4	.5030	.5003	.5941	.5934	.4990	.4980	<b>JSI-0809-04</b>
1/2	19/32	3/8	.5030	.5003	.5941	.5934	.4990	.4980	<b>JSI-0809-06</b>
1/2	19/32	1/2	.5030	.5003	.5941	.5934	.4990	.4980	<b>JSI-0809-08</b>
1/2	19/32	5/8	.5030	.5003	.5941	.5934	.4990	.4980	<b>JSI-0809-10</b>
1/2	19/32	3/4	.5030	.5003	.5941	.5934	.4990	.4980	<b>JSI-0809-12</b>
1/2	19/32	1	.5030	.5003	.5941	.5934	.4990	.4980	<b>JSI-0809-16</b>
1/2	5/8	1/2	.5040	.5013	.6260	.6250	.5000	.4990	<b>JSI-0810-08</b>
1/2	5/8	3/4	.5040	.5013	.6260	.6250	.5000	.4990	<b>JSI-0810-12</b>
9/16	21/32	1/2	.5655	.5627	.6566	.6559	.5615	.5605	<b>JSI-0910-08</b>
9/16	21/32	5/8	.5655	.5627	.6566	.6559	.5615	.5605	<b>JSI-0910-10</b>
9/16	21/32	3/4	.5655	.5627	.6566	.6559	.5615	.5605	<b>JSI-0910-12</b>
5/8	23/32	1/2	.6280	.6253	.7192	.7184	.6240	.6230	<b>JSI-1011-08</b>
5/8	23/32	3/4	.6280	.6253	.7192	.7184	.6240	.6230	<b>JSI-1011-12</b>
5/8	23/32	1	.6280	.6253	.7192	.7184	.6240	.6230	<b>JSI-1011-16</b>
5/8	3/4	1/4	.6297	.6270	.7510	.7500	.6250	.6240	<b>JSI-1012-04</b>
5/8	3/4	3/8	.6297	.6270	.7510	.7500	.6250	.6240	<b>JSI-1012-06</b>
5/8	3/4	1/2	.6297	.6270	.7510	.7500	.6250	.6240	<b>JSI-1012-08</b>
5/8	3/4	3/4	.6297	.6270	.7510	.7500	.6250	.6240	<b>JSI-1012-12</b>
5/8	3/4	1	.6297	.6270	.7510	.7500	.6250	.6240	<b>JSI-1012-16</b>
3/4	7/8	1/2	.7541	.7505	.8755	.8747	.7491	.7479	<b>JSI-1214-08</b>
3/4	7/8	3/4	.7541	.7505	.8755	.8747	.7491	.7479	<b>JSI-1214-12</b>
3/4	7/8	1	.7541	.7505	.8755	.8747	.7491	.7479	<b>JSI-1214-16</b>
3/4	1	3/4	.7559	.7525	1.0010	1.0000	.7500	.7490	<b>JSI-1216-12</b>
3/4	1	1	.7559	.7525	1.0010	1.0000	.7500	.7490	<b>JSI-1216-16</b>
7/8	1	1/2	.8791	.8757	1.0005	.9997	.8741	.8729	<b>JSI-1416-08</b>
7/8	1	3/4	.8791	.8757	1.0005	.9997	.8741	.8729	<b>JSI-1416-12</b>
7/8	1	1	.8791	.8757	1.0005	.9997	.8741	.8729	<b>JSI-1416-16</b>
7/8	1 1/8	3/4	.8809	.8775	1.1260	1.1250	.8750	.8740	<b>JSI-1418-12</b>
7/8	1 1/8	1 1/2	.8809	.8775	1.1260	1.1250	.8750	.8740	<b>JSI-1418-24</b>
1	1 1/8	1/2	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>JSI-1618-08</b>
1	1 1/8	3/4	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>JSI-1618-12</b>
1	1 1/8	1	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>JSI-1618-16</b>
1	1 1/4	1	1.0059	1.0025	1.2510	1.2500	1.0000	.9990	<b>JSI-1620-16</b>
1	1 1/4	1 1/2	1.0059	1.0025	1.2510	1.2500	1.0000	.9990	<b>JSI-1620-24</b>
1 1/8	1 1/4	3/4	1.1288	1.2808	1.2818	1.2808	1.1238	1.1226	<b>JSI-1820-12</b>
1 1/8	1 1/4	1	1.1288	1.2808	1.2818	1.2808	1.1238	1.1226	<b>JSI-1820-16</b>
1 1/8	1 1/4	1 1/4	1.1288	1.2808	1.2818	1.2808	1.1238	1.1226	<b>JSI-1820-20</b>
1 1/8	1 13/8	1	1.1327	1.1276	1.3760	1.3750	1.1250	1.1240	<b>JSI-1822-16</b>
1 1/4	1 13/32	3/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>JSI-2022-12</b>
1 1/4	1 13/32	7/8	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>JSI-2022-14</b>
1 1/4	1 13/32	1	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>JSI-2022-16</b>
1 1/4	1 13/32	1 1/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>JSI-2022-20</b>
1 1/4	1 1/2	1 1/2	1.2600	1.2532	1.5005	1.4995	1.2500	1.2490	<b>JSI-2024-24</b>
1 1/2	1 21/32	1	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>JSI-2426-16</b>

<sup>3)</sup> nach dem Einpressen. Messverfahren ► Seite 57

d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
1 1/2	1 21/32	1 1/2	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>JSI-2426-24</b>
1 1/2	1 3/4	1 1/2	1.5100	1.5032	1.7505	1.7495	1.50	1.499	<b>JSI-2428-24</b>
1 5/8	1 25/32	1	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	<b>JSI-2629-16</b>
1 5/8	1 25/32	1 1/2	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	<b>JSI-2629-24</b>
1 5/8	1 25/32	1 1/2	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	<b>JSI-2629-24</b>
1 3/4	1 15/16	1	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	<b>JSI-2831-16</b>
1 3/4	1 15/16	2	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	<b>JSI-2831-32</b>
1 7/8	2 1/16	1	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	<b>JSI-3033-16</b>
1 7/8	2 1/16	2	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	<b>JSI-3033-32</b>
2	2 3/16	1	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>JSI-3235-16</b>
2	2 3/16	2	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>JSI-3235-32</b>

iglidur® J3 Kapitel ► Seite 165


d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
1/8	3/16	3/16	0.1269	0.1251	0.1878	0.1873	0.1243	0.1236	<b>J3SI-0203-03</b>
3/16	1/4	1/4	0.1892	0.1873	0.2503	0.2497	0.1865	0.1858	<b>J3SI-0304-04</b>
3/16	1/4	3/8	0.1892	0.1873	0.2503	0.2497	0.1865	0.1858	<b>J3SI-0304-06</b>
1/4	5/16	3/8	0.2521	0.2498	0.3128	0.3122	0.2490	0.2481	<b>J3SI-0405-06</b>
1/4	5/16	1/2	0.2521	0.2498	0.3128	0.3122	0.2490	0.2481	<b>J3SI-0405-08</b>
5/16	3/8	1/4	0.3148	0.3125	0.3753	0.3747	0.3115	0.3106	<b>J3SI-0506-04</b>
5/16	3/8	3/8	0.3148	0.3125	0.3753	0.3747	0.3115	0.3106	<b>J3SI-0506-06</b>
5/16	3/8	1/2	0.3148	0.3125	0.3753	0.3747	0.3115	0.3106	<b>J3SI-0506-08</b>
3/8	15/32	1/4	0.3773	0.3750	0.4691	0.4684	0.3740	0.3731	<b>J3SI-0607-04</b>
3/8	15/32	3/8	0.3773	0.3750	0.4691	0.4684	0.3740	0.3731	<b>J3SI-0607-06</b>
3/8	15/32	1/2	0.3773	0.3750	0.4691	0.4684	0.3740	0.3731	<b>J3SI-0607-08</b>
3/8	15/32	5/8	0.3773	0.3750	0.4691	0.4684	0.3740	0.3731	<b>J3SI-0607-10</b>
3/8	15/32	3/4	0.3773	0.3750	0.4691	0.4684	0.3740	0.3731	<b>J3SI-0607-12</b>
7/16	17/32	1/2	0.4406	0.4379	0.5316	0.5309	0.4365	0.4355	<b>J3SI-0708-08</b>
7/16	17/32	3/4	0.4406	0.4379	0.5316	0.5309	0.4365	0.4355	<b>J3SI-0708-12</b>
1/2	19/32	1/4	0.5030	0.5003	0.5941	0.5934	0.4990	0.4980	<b>J3SI-0809-04</b>
1/2	19/32	3/8	0.5030	0.5003	0.5941	0.5934	0.4990	0.4980	<b>J3SI-0809-06</b>
1/2	19/32	1/2	0.5030	0.5003	0.5941	0.5934	0.4990	0.4980	<b>J3SI-0809-08</b>
1/2	19/32	5/8	0.5030	0.5003	0.5941	0.5934	0.4990	0.4980	<b>J3SI-0809-10</b>
1/2	19/32	3/4	0.5030	0.5003	0.5941	0.5934	0.4990	0.4980	<b>J3SI-0809-12</b>
1/2	19/32	1	0.5030	0.5003	0.5941	0.5934	0.4990	0.4980	<b>J3SI-0809-16</b>
9/16	21/32	1/2	0.5655	0.5627	0.6566	0.6559	0.5615	0.5605	<b>J3SI-0910-08</b>
9/16	21/32	5/8	0.5655	0.5627	0.6566	0.6559	0.5615	0.5605	<b>J3SI-0910-10</b>
9/16	21/32	3/4	0.5655	0.5627	0.6566	0.6559	0.5615	0.5605	<b>J3SI-0910-12</b>
5/8	23/32	1/2	0.6280	0.6253	0.7192	0.7184	0.6240	0.6230	<b>J3SI-1011-08</b>
5/8	23/32	3/4	0.6280	0.6253	0.7192	0.7184	0.6240	0.6230	<b>J3SI-1011-12</b>
5/8	23/32	1	0.6280	0.6253	0.7192	0.7184	0.6240	0.6230	<b>J3SI-1011-16</b>
3/4	7/8	1/2	0.7541	0.7505	0.8755	0.8747	0.7491	0.7479	<b>J3SI-1214-08</b>
3/4	7/8	3/4	0.7541	0.7505	0.8755	0.8747	0.7491	0.7479	<b>J3SI-1214-12</b>
3/4	7/8	1	0.7541	0.7505	0.8755	0.8747	0.7491	0.7479	<b>J3SI-1214-16</b>

<sup>3)</sup> nach dem Einpressen. Messverfahren ► Seite 57



Dimensions thrust washer Abmessungen Anlaufscheiben [mm]


Part No. Art.-Nr.	d1	d2	s	d4 h13	d5
GTM-0825-015	8	25	1.5	-	-
GTM-1220-010	12	20	1	-	-
GTM-4060-035	40	60	3.5	-	-
JTM-0615-015	6	15	1.5	-	-
JTM-0815-015	8	15	1.5	-	-
JTM-0818-015	8	18	1.5	13	1.5
JTM-1018-010	10	18	1	-	-
JTM-2644-015	26	44	1.5	35	3
JTM-6290-020	62	90	2	-	-



Dimensions sleeve  
Abmessungen zylindrisch [inch]


Part No. Art.-Nr.	d1	d1 tolerance d1-Toleranz	d2	b1 h13
A181SI-0406-06	1/4	+0.2539 +0.2516	3/8	3/8
GSI-1216-08	3/4	+0.7590 +0.7560	1	1/2
GSI-1620-55	1	+1.0092 +1.0062	1 1/4	55/16
GSI-1620-14	1	+1.0092 +1.0062	1 1/4	7/8
GSI-1620-44	1	+1.0092 +1.0062	1 1/4	11/4
GSI-2428-44	1 1/2	+1.5107 +1.5067	1 3/4	11/4
GSI-2428-20	1 1/2	+1.5107 +1.5067	1 3/4	1 1/4
GSI-5659-48	3 1/2	+3.5830 +3.5028	59/16	3
H1SI-0810-12	1/2	+0.5034 +0.5006	5/8	3/4

Part No. Art.-Nr.	d1	d1 tolerance d1-Toleranz	d2	b1 h13
JSI-1011-10	5/8	+0.6280 +0.6253	23/32	5/8
JSI-1011-14	5/8	+0.6280 +0.6253	23/32	7/8
JSI-1011-20	5/8	+0.6280 +0.6253	23/32	1 1/4
JSI-2226-32	1 3/8	+1.3809 +1.3770	1 5/8	2
Q2SI-4852-48	3	+3.0071 +3.0024	3 1/4	3
QSI-2428-16	1 1/2	+1.5059 +1.5020	1 3/4	1
QSI-2428-24	1 1/2	+1.5059 +1.5020	1 3/4	1
QSI-2428-40	1 1/2	+1.5059 +1.5020	1 3/4	5/2



Dimensions clips bearing  
Abmessungen Clipslager [mm]

Part No. Art.-Nr.	d1	d2	d3	d4	s	b1
MCM-12-018	12.0	13.6	14.4	17.0	0.8	3.4



Dimensions split bearing  
Abmessungen Schlitzlager [inch]

Part No. Art.-Nr.	d1	d2	b1	d3	b2
MYI-05-10	5/16	0.3744	5/8	1/2	0.0299



Dimensions with flange  
Abmessungen mit Bund [inch]

Part No. Art.-Nr.	d1	d1 tolerance d1-Toleranz	d2	d3	b1 h13	b2
GFI-1012-08	5/8	+0.6297 +0.6270	3/4	1/2	1	0.062
GFI-1012-12	5/8	+0.6297 +0.6270	3/4	3/4	1	0.062
GFI-1012-16	5/8	+0.6297 +0.6270	3/4	1	1	0.062
GFI-1214-18	3/4	+0.7541 +0.7505	7/8	1 1/4	1.125	0.062
ZFI-0304-06	3/16	+0.1888 +0.1869	1/4	3/8	0.375	0.032

Calculate online Online berechenbar  
[www.igus.eu/iglidur-experte](http://www.igus.eu/iglidur-experte)  
[www.igus.de/iglidur-expert](http://www.igus.de/iglidur-expert)

Available Lieferbar  
 from stock ab Lager

[www.igus.de/iglidur](http://www.igus.de/iglidur)  
[www.igus.eu/iglidur](http://www.igus.eu/iglidur)

Calculate online Online berechenbar  
[www.igus.eu/iglidur-experte](http://www.igus.eu/iglidur-experte)  
[www.igus.de/iglidur-expert](http://www.igus.de/iglidur-expert)

Available Lieferbar  
 from stock ab Lager

[www.igus.de/iglidur](http://www.igus.de/iglidur)  
[www.igus.eu/iglidur](http://www.igus.eu/iglidur)