


E GZ M - 05 - 50



Special Properties

- Maintenance-free, self-lubricating
- Mechanical joining link between 2 components
- Self-aligning to compensate for angular errors

Special lengths are usually possible, please contact us



Material

Housing: igumid G

► Page 70.6

Spherical Bearing:

iglidur® W300

► Chapter 5

Load Data and Dimensions [mm] – igubal® – Double Joint EGZM

Part Number	Maximum Static Radial Tensile Strength		Maximum Static Axial Compressive Strength		d1 [mm]	d2 [mm]	X [mm]	b [mm]	a [mm]
	Short term [N]	Long term [N]	Short term [N]	Long term [N]					
EGZM-04-25	1100	550	1300	650	04	20	25	4	10
EGZM-04-50	1100	550	750	375	04	20	50	4	10
EGZM-04-75	1100	550	500	250	04	20	75	4	10
EGZM-05-25	1100	550	1300	650	05	20	25	4	10
EGZM-05-50	1100	550	750	375	05	20	50	4	10
EGZM-05-75	1100	550	500	250	05	20	75	4	10
EGZM-06-25	1100	550	1300	650	06	20	25	4	10
EGZM-06-50	1100	550	750	375	06	20	50	4	10
EGZM-06-75	1100	550	500	250	06	20	75	4	10
EGZM-08-60	3000	1500	3500	1750	08	30	60	7	15
EGZM-08-100	3000	1500	1900	950	08	30	100	7	15
EGZM-10-60	2500	1250	3500	1750	10	30	60	7	15
EGZM-10-85	2500	1250	2300	1150	10	30	85	7	15
EGZM-10-100	2500	1250	1900	950	10	30	100	7	15
EGZM-12-60	2000	1000	3500	1750	12	30	60	7	15
EGZM-12-100	2000	1000	1900	950	12	30	100	7	15

Spherical bearing material to choose ► Page 57.3



REM:
Low Cost



JEM: Low moisture absorption



J4VEM: Clearance-free spherical ball
► Page 57.6

