

## Request Form Belt Conveyor

### Customer details

Company:	Date:
Contact person:	Customer-No.:
Factory norm:	
Type of factory standard:	

### Conveyor system and quotation data

Conveyor system:	Customer specifications
Quotation position:	Quantity:
Customer reference:	

### Material to be conveyed and environmental conditions

Material to be conveyed :	Weight per piece (kg):
Total load max. (kg):	Line load (kg/m):
Dimensions L/W/H (mm):	Enclosed drawing      Enclosed sample
Transport orientation:	Short Side Leading (transversely)      Long Side Leading (lengthways)
Temperature (°C)	Material to be conveyed:      Environment:
Environment:	clean      dirty
Type of contamination:	
Material to be conveyed:	clean      dirty
Type of contamination:	
Special features:	

### Conveyor specification

Belt length L (mm):	Belt width B (mm):
Infeed idler:	Outfeed idler:
Lateral forces	yes      no      Customer drawings

# Request Form Belt Conveyor

## Drive and motor

Drive version:			
Motor position:		Output quantity: pcs/min	
Speed: m/min at 50 Hz,		constant adjustable	
Motor orientation:		Motor manufacturer:	
Operating mode:		Power transmission:	
Cycling operation: Cycles/min		Transport time (s) Downtime (s)	
Voltage: 230/400V 50 Hz		180/200V, DC Other:	
Speed control:		with support bracket no support bracket	

## Belt

Belt type:		Other type:	
good traction accumulation		antistatic FDA-Belt	
Special features:			
Belt colour:			
Long. cleats:		Height (mm): Spacing (mm):	
Lateral cleats:		Height (mm): Spacing (mm):	
Sidewalls:		Height (mm): Spacing (mm):	

## Side rails

Type of side rail:		Side rail version:	
Height:		Usable width:	
Side-rail positioning: both sides		right side left side	

## Stands

Type of stand:	
Quantity	Working height (mm):

## Request Form Belt Conveyor

### Documentation/Drawings:

CAD format for customer	2D-DXF	DWG	3D (Step)		
Quotation drawing:	yes	no	Approval drawing	yes	no
Paper documentation:	English	pcs.	German	pcs.	Other language: pcs.
Digital documentation:	English	pcs.	German	pcs.	Other language: pcs.

**Observations / functional description / additional options**