


Serie 2208 - im Innen- und Außenradius zu öffnen



R [mm]	K	T [mm]
055	265	046
063	290	046
075	330	046
100	410	046
125	485	046
150	565	046

Bestellbeispiel

2208, 062, 75/ 300, 0

- Farbe
- Außenradius
- Innenradius
- Breiten-Index
- Serie

Bi [mm]	Ba [mm]	AR [mm]	IR [mm]	R 055 mm 2208....	R 063 mm 2208....	R 075 mm 2208....	R 100 mm 2208....	R 125 mm 2208....	R150 mm 2208....	Gewicht [kg/m]
52,5	80	300	227	.052.055/300	.052.063/300	.052.075/300	.052.100/300	.052.125/300	.052.150/300	≈ 1,20
62,5	90	300	217	-	-	.062.075/300	.062.100/300	.062.125/300	.062.150/300	≈ 1,24
74,5	102	300	205	-	-	-	.074.100/300	.074.125/300	.074.150/300	≈ 1,29
87,5	115	300	192	-	-	-	.087.100/300	.087.125/300	.087.150/300	≈ 1,35
112,5	140	300	167	-	-	-	-	.112.125/300	.112.150/300	≈ 1,46



**Innenaufteilung** - Für die Innenaufteilung können alle Elemente (außer Seitenplatten) aus der Serie E4.28 verwendet werden ▶ Seite 7.34

