


Part No. structure



## Series R09 E-Tube - zip-open along the outer radius

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending Radii	Weight [kg/m]
R09.10. <input type="text"/> .0	10	18,2	048	075 100	≈ 0,21
R09.16. <input type="text"/> .0	16	24,2	048	075 100	≈ 0,24
R09.20. <input type="text"/> .0	20	28,2	048	075 100	≈ 0,25
R09.30. <input type="text"/> .0	30	38,2	048	075 100	≈ 0,28
R09.40. <input type="text"/> .0	40	48,2	048	075 100	≈ 0,31
R09.50. <input type="text"/> .0	50	58,2	048	075 100	≈ 0,34

Supplement part no. with required radius ( $R$ ) Example: R09.20.  048  .0

0 = standard color, other colors ► page 1.39 · Pitch = 20 mm/link - Links/m = 50



Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222

igus® GmbH  
51147 Cologne

Internet: [www.igus.eu](http://www.igus.eu)  
E-mail: [info@igus.de](mailto:info@igus.de)