


## SERIES 63



### VULKOLLAN® WHEELS, CAST IRON CENTRE, SWIVEL TOP PLATE BRACKET TYPE EE MHD

#### Wheel description




**Tread:** Vulkollan® polyurethane tread; hardness 93 +/-2 Shore A

**Centre:** cast iron.

**Hub:** the housing is obtained by moulding and turning and contains ball bearings series Z

#### Bracket description

##### Bracket EE Medium Heavy Duty (max. load capacity 900 daN)



- 1) **Plate:** forged steel with integrated pin
  - 2) **Fork:** drawn sides electrowelded to the flange
  - 3) **Swivel actions:** axial ball bearing and taper roller bearing
  - 4) **Lubricator**
  - 5) **Nut anti-loosening system**
- Finish:** electrolytic galvanisation  
**Fitting:** top plate