


Part No. structure



Series R15 E-Tube - zip-open along the outer radius

Part No.	B_i [mm]	B_a [mm]	R [mm]	Bending Radii							Weight [kg/m]	
R15.025. <input type="text"/> .0	25	36	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	≈ 0,40
R15.038. <input type="text"/> .0	38	49	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	≈ 0,46
R15.063. <input type="text"/> .0	63	76	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	≈ 0,63
R15.080. <input type="text"/> .0	80	94	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	≈ 0,70


More E-Tube widths are available upon request.

Supplement part no. with required radius (R) Example: R15.025. .0

0 = standard color, other colors ▶ page 1.39 · Pitch = 30,5 mm/link - Links/m = 33




Zipper | **Series R15** | Accessories | Interior Separation



Vert. Separator, slotted
unassembled **R153**
assembled **R154**



Option 1: Vertical Separators

- **Vertical Separators** are used if a vertical subdivision of the E-Chain® interior is required
- **Standard** subdivision with **Vertical Separator, slotted 154**, for combinations with **Full-Width Shelf 111.X**
- **By standard** Vertical Separators are assembled every other chain link



Option 2: Full-Width Shelves

- For applications involving many thin cables with similar or identical diameters



Width X [mm]	Part No. unassembled	Part No. assembled
025	110.25	111.25
038	110.38	111.38

Width X [mm]	Part No. unassembled	Part No. assembled
063	110.63	111.63
080	110.80	111.80