

d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
1	1 1/8	1/2	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>A500SI-1618-08</b>
1	1 1/8	3/4	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>A500SI-1618-12</b>
1	1 1/8	1	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>A500SI-1618-16</b>
1 1/8	1 1/4	3/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	<b>A500SI-1820-12</b>
1 1/8	1 1/4	1	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	<b>A500SI-1820-16</b>
1 1/8	1 1/4	1 1/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	<b>A500SI-1820-20</b>
1 1/4	1 13/32	3/4	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	<b>A500SI-2022-12</b>
1 1/4	1 13/32	1	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	<b>A500SI-2022-16</b>
1 1/4	1 13/32	1 1/4	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	<b>A500SI-2022-20</b>
1 1/2	1 21/32	1	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	<b>A500SI-2426-16</b>
1 1/2	1 21/32	1 1/2	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	<b>A500SI-2426-24</b>
1 5/8	1 25/32	1	1.6287	1.6248	1.7818	1.7808	1.6238	1.6222	<b>A500SI-2629-16</b>
1 5/8	1 25/32	1 1/2	1.6287	1.6248	1.7818	1.7808	1.6238	1.6222	<b>A500SI-2629-24</b>
1 3/4	1 15/16	1	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	<b>A500SI-2831-16</b>
1 3/4	1 15/16	2	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	<b>A500SI-2831-32</b>
1 7/8	2 1/16	1	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	<b>A500SI-3033-16</b>
1 7/8	2 1/16	2	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	<b>A500SI-3033-32</b>
2	2 3/16	1	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	<b>A500SI-3235-16</b>
2	2 3/16	2	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	<b>A500SI-3235-32</b>

d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
3/8	8/16	3/4	.3773	.3750	.5015	.5010	.3750	.3741	<b>GSI-0608-12</b>
7/16	17/32	1/4	.4406	.4379	.5316	.5309	.4365	.4355	<b>GSI-0708-04</b>
7/16	17/32	1/2	.4406	.4379	.5316	.5309	.4365	.4355	<b>GSI-0708-08</b>
7/16	17/32	3/4	.4406	.4379	.5316	.5309	.4365	.4355	<b>GSI-0708-12</b>
1/2	19/32	3/16	.5030	.5003	.5941	.5934	.4990	.4980	<b>GSI-0809-03</b>
1/2	19/32	1/4	.5030	.5003	.5941	.5934	.4990	.4980	<b>GSI-0809-04</b>
1/2	19/32	3/8	.5030	.5003	.5941	.5934	.4990	.4980	<b>GSI-0809-06</b>
1/2	19/32	1/2	.5030	.5003	.5941	.5934	.4990	.4980	<b>GSI-0809-08</b>
1/2	19/32	5/8	.5030	.5003	.5941	.5934	.4990	.4980	<b>GSI-0809-10</b>
1/2	19/32	3/4	.5030	.5003	.5941	.5934	.4990	.4980	<b>GSI-0809-12</b>
1/2	19/32	1	.5030	.5003	.5941	.5934	.4990	.4980	<b>GSI-0809-16</b>
1/2	5/8	3/4	.5040	.5013	.6260	.6250	.5000	.4990	<b>GSI-0810-12</b>
9/16	21/32	3/8	.5655	.5627	.6566	.6559	.5615	.5605	<b>GSI-0910-06</b>
9/16	21/32	1/2	.5655	.5627	.6566	.6559	.5615	.5605	<b>GSI-0910-08</b>
9/16	21/32	5/8	.5655	.5627	.6566	.6559	.5615	.5605	<b>GSI-0910-10</b>
9/16	21/32	3/4	.5655	.5627	.6566	.6559	.5615	.5605	<b>GSI-0910-12</b>
5/8	23/32	3/8	.6280	.6253	.7192	.7184	.6240	.6230	<b>GSI-1011-06</b>
5/8	23/32	1/2	.6280	.6253	.7192	.7184	.6240	.6230	<b>GSI-1011-08</b>
5/8	23/32	5/8	.6280	.6253	.7192	.7184	.6240	.6230	<b>GSI-1011-10</b>
5/8	23/32	3/4	.6280	.6253	.7192	.7184	.6240	.6230	<b>GSI-1011-12</b>
5/8	23/32	1	.6280	.6253	.7192	.7184	.6240	.6230	<b>GSI-1011-16</b>
5/8	23/32	1 1/4	.6280	.6253	.7192	.7184	.6240	.6230	<b>GSI-1011-20</b>
5/8	23/32	1 7/8	.6280	.6253	.7192	.7184	.6240	.6230	<b>GSI-1011-30</b>
5/8	3/4	1/2	.6290	.6263	.7510	.7500	.6250	.6240	<b>GSI-1012-08</b>
5/8	3/4	1	.6290	.6263	.7510	.7500	.6250	.6240	<b>GSI-1012-16</b>
11/16	25/32	7/8	.6906	.6879	.7817	.7809	.6865	.6855	<b>GSI-1112-14</b>
3/4	7/8	1/8	.7541	.7505	.8755	.8747	.7491	.7479	<b>GSI-1214-02</b>
3/4	7/8	3/8	.7541	.7505	.8755	.8747	.7491	.7479	<b>GSI-1214-06</b>
3/4	7/8	1/2	.7541	.7505	.8755	.8747	.7491	.7479	<b>GSI-1214-08</b>
3/4	7/8	3/4	.7541	.7505	.8755	.8747	.7491	.7479	<b>GSI-1214-12</b>
3/4	7/8	1	.7541	.7505	.8755	.8747	.7491	.7479	<b>GSI-1214-16</b>
3/4	7/8	1 1/4	.7541	.7505	.8755	.8747	.7491	.7479	<b>GSI-1214-20</b>
3/4	7/8	1 1/2	.7541	.7505	.8755	.8747	.7491	.7479	<b>GSI-1214-24</b>
7/8	1	3/8	.8791	.8757	1.0005	.9997	.8741	.8729	<b>GSI-1416-06</b>
7/8	1	1/2	.8791	.8757	1.0005	.9997	.8741	.8729	<b>GSI-1416-08</b>
7/8	1	5/8	.8791	.8757	1.0005	.9997	.8741	.8729	<b>GSI-1416-10</b>
7/8	1	3/4	.8791	.8757	1.0005	.9997	.8741	.8729	<b>GSI-1416-12</b>
7/8	1	1	.8791	.8757	1.0005	.9997	.8741	.8729	<b>GSI-1416-16</b>
7/8	1	1 1/2	.8791	.8757	1.0005	.9997	.8741	.8729	<b>GSI-1416-24</b>
1	1 1/8	1/2	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>GSI-1618-08</b>
1	1 1/8	3/4	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>GSI-1618-12</b>
1	1 1/8	1	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>GSI-1618-16</b>
1	1 1/8	1 1/4	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>GSI-1618-20</b>
1	1 1/8	1 1/2	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>GSI-1618-24</b>
1	1 1/8	2 1/16	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>GSI-1618-33</b>
1 1/8	1 9/32	3/4	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>GSI-1820-12</b>

**iglidur® G** Kapitel ▶ Seite 79

d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
1/8	3/16	3/16	.1269	.1251	.1878	.1873	.1243	.1236	<b>GSI-0203-03</b>
1/8	3/16	1/4	.1269	.1251	.1878	.1873	.1243	.1236	<b>GSI-0203-04</b>
1/8	3/16	3/8	.1269	.1251	.1878	.1873	.1243	.1236	<b>GSI-0203-06</b>
3/16	1/4	1/4	.1892	.1873	.2503	.2497	.1865	.1858	<b>GSI-0304-04</b>
3/16	1/4	3/8	.1892	.1873	.2503	.2497	.1865	.1858	<b>GSI-0304-06</b>
3/16	1/4	1/2	.1892	.1873	.2503	.2497	.1865	.1858	<b>GSI-0304-08</b>
1/4	5/16	1/4	.2521	.2498	.3128	.3122	.2490	.2481	<b>GSI-0405-04</b>
1/4	5/16	5/16	.2521	.2498	.3128	.3122	.2490	.2481	<b>GSI-0405-05</b>
1/4	5/16	3/8	.2521	.2498	.3128	.3122	.2490	.2481	<b>GSI-0405-06</b>
1/4	5/16	1/2	.2521	.2498	.3128	.3122	.2490	.2481	<b>GSI-0405-08</b>
1/4	5/16	5/8	.2521	.2498	.3128	.3122	.2490	.2481	<b>GSI-0405-10</b>
1/4	5/16	3/4	.2521	.2498	.3128	.3122	.2490	.2481	<b>GSI-0405-12</b>
5/16	3/8	1/4	.3148	.3125	.3753	.3747	.3115	.3106	<b>GSI-0506-04</b>
5/16	3/8	3/8	.3148	.3125	.3753	.3747	.3115	.3106	<b>GSI-0506-06</b>
5/16	3/8	1/2	.3148	.3125	.3753	.3747	.3115	.3106	<b>GSI-0506-08</b>
5/16	3/8	3/4	.3148	.3125	.3753	.3747	.3115	.3106	<b>GSI-0506-12</b>
3/8	15/32	1/4	.3773	.3750	.4691	.4684	.3740	.3731	<b>GSI-0607-04</b>
3/8	15/32	3/8	.3773	.3750	.4691	.4684	.3740	.3731	<b>GSI-0607-06</b>
3/8	15/32	1/2	.3773	.3750	.4691	.4684	.3740	.3731	<b>GSI-0607-08</b>
3/8	15/32	5/8	.3773	.3750	.4691	.4684	.3740	.3731	<b>GSI-0607-10</b>
3/8	15/32	3/4	.3773	.3750	.4691	.4684	.3740	.3731	<b>GSI-0607-12</b>
3/8	8/16	1/2	.3783	.3760	.5015	.5010	.3750	.3741	<b>GSI-0608-08</b>

<sup>3)</sup> nach dem Einpressen. Messverfahren ▶ Seite 57

<sup>3)</sup> nach dem Einpressen. Messverfahren ▶ Seite 57

d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
1 1/8	1 1/4	1	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>GSI-1820-16</b>
1 1/8	1 1/4	1 1/4	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>GSI-1820-20</b>
1 1/8	1 9/32	1 1/2	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>GSI-1820-24</b>
1 1/4	1 13/32	3/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>GSI-2022-12</b>
1 1/4	1 13/32	7/8	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>GSI-2022-14</b>
1 1/4	1 13/32	1	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>GSI-2022-16</b>
1 1/4	1 13/32	1 1/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>GSI-2022-20</b>
1 1/4	1 13/32	1 1/2	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>GSI-2022-24</b>
1 3/8	1 17/32	1	1.3798	1.3758	1.5318	1.5308	1.3738	1.3722	<b>GSI-2224-16</b>
1 3/8	1 17/32	1 1/2	1.3798	1.3758	1.5318	1.5308	1.3738	1.3722	<b>GSI-2224-24</b>
1 3/8	1 17/32	1 5/8	1.3798	1.3758	1.5318	1.5308	1.3738	1.3722	<b>GSI-2224-26</b>
1 1/2	1 21/32	3/8	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>GSI-2426-06</b>
1 1/2	1 21/32	7/16	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>GSI-2426-07</b>
1 1/2	1 21/32	1/2	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>GSI-2426-08</b>
1 1/2	1 21/32	3/4	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>GSI-2426-12</b>
1 1/2	1 21/32	1	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>GSI-2426-16</b>
1 1/2	1 21/32	1 1/2	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>GSI-2426-24</b>
1 5/8	1 25/32	1	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	<b>GSI-2629-16</b>
1 5/8	1 25/32	1 1/4	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	<b>GSI-2629-20</b>
1 5/8	1 25/32	1 1/2	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	<b>GSI-2629-24</b>
1 3/4	1 15/16	1	1.7547	1.7505	1.9381	1.9371	1.7487	1.7471	<b>GSI-2831-16</b>
1 3/4	1 15/16	1 1/2	1.7547	1.7505	1.9381	1.9371	1.7487	1.7471	<b>GSI-2831-24</b>
1 3/4	1 15/16	2	1.7547	1.7505	1.9381	1.9371	1.7487	1.7471	<b>GSI-2831-32</b>
1 3/4	1 15/16	2 1/2	1.7547	1.7505	1.9381	1.9371	1.7487	1.7471	<b>GSI-2831-40</b>
1 3/4	1 15/16	3	1.7547	1.7505	1.9381	1.9371	1.7487	1.7471	<b>GSI-2831-48</b>
1 7/8	2 1/16	1	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	<b>GSI-3033-16</b>
1 7/8	2 1/16	2	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	<b>GSI-3033-32</b>
2	2 3/16	1	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>GSI-3235-16</b>
2	2 3/16	1 1/2	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>GSI-3235-24</b>
2	2 3/16	2	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>GSI-3235-32</b>
2 1/4	2 7/16	2	2.2577	2.2531	2.4377	2.4365	2.2507	2.2489	<b>GSI-3639-32</b>
2 2/4	2 11/16	2	2.5082	2.5035	2.6881	2.6869	2.5000	2.4999	<b>GSI-4043-32</b>
2 3/4	2 15/16	2	2.7570	2.7523	2.9370	2.9358	2.7500	2.7490	<b>GSI-4447-32</b>
3	3 3/16	2	3.0070	3.0023	3.1870	3.1858	3.0000	2.9990	<b>GSI-4851-32</b>

iglidur® H1 Kapitel ► Seite 297

d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			h13	max.	min.	max.	min.	max.	
1/8	3/16	3/16	.1266	.1247	.1878	.1873	.1243	.1236	<b>H1SI-0203-03</b>
3/16	1/4	1/4	.1888	.1869	.2503	.2497	.1865	.1858	<b>H1SI-0304-04</b>
3/16	1/4	3/8	.1888	.1869	.2503	.2497	.1865	.1858	<b>H1SI-0304-06</b>
1/4	5/16	3/8	.2518	.2495	.3128	.3122	.2490	.2481	<b>H1SI-0405-06</b>
1/4	5/16	1/2	.2518	.2495	.3128	.3122	.2490	.2481	<b>H1SI-0405-08</b>
5/16	3/8	1/4	.3143	.3120	.3753	.3747	.3115	.3106	<b>H1SI-0506-04</b>

<sup>3)</sup> nach dem Einpressen. Messverfahren ► Seite 57

d1	d2	b1	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
			h13	max.	min.	max.	min.	max.	
5/16	3/8	3/8	.3143	.3120	.3753	.3747	.3115	.3106	<b>H1SI-0506-06</b>
5/16	3/8	1/2	.3143	.3120	.3753	.3747	.3115	.3106	<b>H1SI-0506-08</b>
3/8	15/32	1/4	.3768	.3745	.4691	.4684	.3740	.3731	<b>H1SI-0607-04</b>
3/8	15/32	3/8	.3768	.3745	.4691	.4684	.3740	.3731	<b>H1SI-0607-06</b>
3/8	15/32	1/2	.3768	.3745	.4691	.4684	.3740	.3731	<b>H1SI-0607-08</b>
3/8	15/32	5/8	.3768	.3745	.4691	.4684	.3740	.3731	<b>H1SI-0607-10</b>
3/8	15/32	3/4	.3768	.3745	.4691	.4684	.3740	.3731	<b>H1SI-0607-12</b>
7/16	17/32	1/2	.4399	.4371	.5316	.5309	.4365	.4355	<b>H1SI-0708-08</b>
7/16	17/32	3/4	.4399	.4371	.5316	.5309	.4365	.4355	<b>H1SI-0708-12</b>
1/2	19/32	1/4	.5024	.4996	.5941	.5934	.4990	.4980	<b>H1SI-0809-04</b>
1/2	19/32	3/8	.5024	.4996	.5941	.5934	.4990	.4980	<b>H1SI-0809-06</b>
1/2	19/32	1/2	.5024	.4996	.5941	.5934	.4990	.4980	<b>H1SI-0809-08</b>
1/2	19/32	5/8	.5024	.4996	.5941	.5934	.4990	.4980	<b>H1SI-0809-10</b>
1/2	19/32	3/4	.5024	.4996	.5941	.5934	.4990	.4980	<b>H1SI-0809-12</b>
1/2	19/32	1	.5024	.4996	.5941	.5934	.4990	.4980	<b>H1SI-0809-16</b>
9/16	21/32	1/2	.5649	.5620	.6566	.6559	.5615	.5605	<b>H1SI-0910-08</b>
9/16	21/32	5/8	.5649	.5620	.6566	.6559	.5615	.5605	<b>H1SI-0910-10</b>
9/16	21/32	3/4	.5649	.5620	.6566	.6559	.5615	.5605	<b>H1SI-0910-12</b>
5/8	23/32	1/2	.6274	.6246	.7192	.7184	.6240	.6230	<b>H1SI-1011-08</b>
5/8	23/32	3/4	.6274	.6246	.7192	.7184	.6240	.6230	<b>H1SI-1011-12</b>
5/8	23/32	1	.6274	.6246	.7192	.7184	.6240	.6230	<b>H1SI-1011-16</b>
3/4	7/8	1/2	.7532	.7499	.8755	.8747	.7491	.7479	<b>H1SI-1214-08</b>
3/4	7/8	3/4	.7532	.7499	.8755	.8747	.7491	.7479	<b>H1SI-1214-12</b>
3/4	7/8	1	.7532	.7499	.8755	.8747	.7491	.7479	<b>H1SI-1214-16</b>
7/8	1	1/2	.8782	.8749	1.0005	.9997	.8741	.8729	<b>H1SI-1416-08</b>
7/8	1	3/4	.8782	.8749	1.0005	.9997	.8741	.8729	<b>H1SI-1416-12</b>
7/8	1	1	.8782	.8749	1.0005	.9997	.8741	.8729	<b>H1SI-1416-16</b>
1	1 1/8	1/2	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>H1SI-1618-08</b>
1	1 1/8	3/4	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>H1SI-1618-12</b>
1	1 1/8	1	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>H1SI-1618-16</b>
1 1/8	1 1/4	3/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	<b>H1SI-1820-12</b>
1 1/8	1 1/4	1	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	<b>H1SI-1820-16</b>
1 1/8	1 1/4	1 1/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	<b>H1SI-1820-20</b>
1 1/4	1 13/32	3/4	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	<b>H1SI-2022-12</b>
1 1/4	1 13/32	1	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	<b>H1SI-2022-16</b>
1 1/4	1 13/32	1 1/4	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	<b>H1SI-2022-20</b>
1 1/2	1 21/32	1	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	<b>H1SI-2426-16</b>
1 1/2	1 21/32	1 1/2	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	<b>H1SI-2426-24</b>
1 5/8	1 25/32	1	1.6287	1.6248	1.7818	1.7808	1.6238	1.6222	<b>H1SI-2629-16</b>
1 5/8	1 25/32	1 1/2	1.6287	1.6248	1.7818	1.7808	1.6238	1.6222	<b>H1SI-2629-24</b>
1 3/4	1 15/16	1	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	<b>H1SI-2831-16</b>
1 3/4	1 15/16	2	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	<b>H1SI-2831-32</b>
1 7/8	2 1/16	1	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	<b>H1SI-3033-16</b>
1 7/8	2 1/16	2	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	<b>H1SI-3033-32</b>
2	2 3/16	1	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	<b>H1SI-3235-16</b>
2	2 3/16	2	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	<b>H1SI-3235-32</b>

<sup>3)</sup> nach dem Einpressen. Messverfahren ► Seite 57



Dimensions thrust washer Abmessungen Anlaufscheiben [mm]


Part No. Art.-Nr.	d1	d2	s	d4 h13	d5
GTM-0825-015	8	25	1.5	-	-
GTM-1220-010	12	20	1	-	-
GTM-4060-035	40	60	3.5	-	-
JTM-0615-015	6	15	1.5	-	-
JTM-0815-015	8	15	1.5	-	-
JTM-0818-015	8	18	1.5	13	1.5
JTM-1018-010	10	18	1	-	-
JTM-2644-015	26	44	1.5	35	3
JTM-6290-020	62	90	2	-	-



Dimensions sleeve  
Abmessungen zylindrisch [inch]


Part No. Art.-Nr.	d1	d1 tolerance d1-Toleranz	d2	b1 h13
A181SI-0406-06	1/4	+0.2539 +0.2516	3/8	3/8
GSI-1216-08	3/4	+0.7590 +0.7560	1	1/2
GSI-1620-55	1	+1.0092 +1.0062	1 1/4	55/16
GSI-1620-14	1	+1.0092 +1.0062	1 1/4	7/8
GSI-1620-44	1	+1.0092 +1.0062	1 1/4	11/4
GSI-2428-44	1 1/2	+1.5107 +1.5067	1 3/4	11/4
GSI-2428-20	1 1/2	+1.5107 +1.5067	1 3/4	1 1/4
GSI-5659-48	3 1/2	+3.5830 +3.5028	59/16	3
H1SI-0810-12	1/2	+0.5034 +0.5006	5/8	3/4

Part No. Art.-Nr.	d1	d1 tolerance d1-Toleranz	d2	b1 h13
JSI-1011-10	5/8	+0.6280 +0.6253	23/32	5/8
JSI-1011-14	5/8	+0.6280 +0.6253	23/32	7/8
JSI-1011-20	5/8	+0.6280 +0.6253	23/32	1 1/4
JSI-2226-32	1 3/8	+1.3809 +1.3770	1 5/8	2
Q2SI-4852-48	3	+3.0071 +3.0024	3 1/4	3
QSI-2428-16	1 1/2	+1.5059 +1.5020	1 3/4	1
QSI-2428-24	1 1/2	+1.5059 +1.5020	1 3/4	1
QSI-2428-40	1 1/2	+1.5059 +1.5020	1 3/4	5/2



Dimensions clips bearing  
Abmessungen Clipslager [mm]

Part No. Art.-Nr.	d1	d2	d3	d4	s	b1
MCM-12-018	12.0	13.6	14.4	17.0	0.8	3.4



Dimensions split bearing  
Abmessungen Schlitzlager [inch]

Part No. Art.-Nr.	d1	d2	b1	d3	b2
MYI-05-10	5/16	0.3744	5/8	1/2	0.0299



Dimensions with flange  
Abmessungen mit Bund [inch]

Part No. Art.-Nr.	d1	d1 tolerance d1-Toleranz	d2	d3	b1 h13	b2
GFI-1012-08	5/8	+0.6297 +0.6270	3/4	1/2	1	0.062
GFI-1012-12	5/8	+0.6297 +0.6270	3/4	3/4	1	0.062
GFI-1012-16	5/8	+0.6297 +0.6270	3/4	1	1	0.062
GFI-1214-18	3/4	+0.7541 +0.7505	7/8	1 1/4	1.125	0.062
ZFI-0304-06	3/16	+0.1888 +0.1869	1/4	3/8	0.375	0.032

Calculate online Online berechenbar  
[www.igus.eu/iglidur-experte](http://www.igus.eu/iglidur-experte)  
[www.igus.de/iglidur-expert](http://www.igus.de/iglidur-expert)

Available Lieferbar  
 from stock ab Lager

[www.igus.de/iglidur](http://www.igus.de/iglidur)  
[www.igus.eu/iglidur](http://www.igus.eu/iglidur)

Calculate online Online berechenbar  
[www.igus.eu/iglidur-experte](http://www.igus.eu/iglidur-experte)  
[www.igus.de/iglidur-expert](http://www.igus.de/iglidur-expert)

Available Lieferbar  
 from stock ab Lager

[www.igus.de/iglidur](http://www.igus.de/iglidur)  
[www.igus.eu/iglidur](http://www.igus.eu/iglidur)