

d1	d2	b1	d1 ³⁾		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
5/8	23/32	1	.6280	.6253	.7192	.7184	.6240	.6230	WSI-1011-16
11/16	25/32	3/4	.6906	.6879	.7817	.7809	.6865	.6855	WSI-1112-12
3/4	7/8	1/2	.7541	.7507	.8755	.8747	.7491	.7479	WSI-1214-08
3/4	7/8	3/4	.7541	.7507	.8755	.8747	.7491	.7479	WSI-1214-12
3/4	7/8	1	.7541	.7507	.8755	.8747	.7491	.7479	WSI-1214-16
3/4	7/8	1 1/2	.7541	.7507	.8755	.8747	.7491	.7479	WSI-1214-24
7/8	1	1/4	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-04
7/8	1	3/8	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-06
7/8	1	1/2	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-08
7/8	1	5/8	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-10
7/8	1	3/4	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-12
7/8	1	1	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-16
7/8	1	1 1/2	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-24
1	1 1/8	3/8	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-06
1	1 1/8	1/2	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-08
1	1 1/8	3/4	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-12
1	1 1/8	1	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-16
1	1 1/8	1 5/16	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-20
1	1 1/8	1 3/8	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-22
1	1 1/8	1 1/2	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-24
1 1/8	1 1/4	3/4	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	WSI-1820-12
1 1/8	1 1/4	1	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	WSI-1820-16
1 1/8	1 1/4	1 1/4	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	WSI-1820-20
1 1/4	1 13/32	3/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-12
1 1/4	1 13/32	7/8	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-14
1 1/4	1 13/32	1	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-16
1 1/4	1 13/32	1 1/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-20
1 1/4	1 13/32	1 1/2	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-24
1 3/8	1 17/32	1	1.3798	1.3758	1.5318	1.5308	1.3738	1.3722	WSI-2224-16
1 3/8	1 17/32	1 1/2	1.3798	1.3758	1.5318	1.5308	1.3738	1.3722	WSI-2224-24
1 1/2	1 21/32	3/4	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	WSI-2426-12
1 1/2	1 21/32	1	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	WSI-2426-16
1 1/2	1 21/32	1 1/2	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	WSI-2426-24
1 1/2	1 21/32	2 3/4	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	WSI-2426-44
1 5/8	1 25/32	1	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	WSI-2629-16
1 5/8	1 25/32	1 1/4	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	WSI-2629-20
1 5/8	1 25/32	1 1/2	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	WSI-2629-24
1 3/4	1 15/16	1	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	WSI-2831-16
1 3/4	1 15/16	1 1/2	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	WSI-2831-24
1 3/4	1 15/16	2	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	WSI-2831-32
1 3/4	1 15/16	3	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	WSI-2831-48
1 7/8	2 1/16	1	1.8747	1.8786	2.0621	2.0633	1.8721	1.8737	WSI-3033-16
1 7/8	2 1/16	2	1.8747	1.8786	2.0621	2.0633	1.8721	1.8737	WSI-3033-32
2	2 3/16	1	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	WSI-3235-16
2	2 3/16	1 1/2	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	WSI-3235-24
2	2 3/16	2	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	WSI-3235-32

³⁾ nach dem Einpressen. Messverfahren ► Seite 57

d1	d2	b1	d1 ³⁾		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
2 1/4	2 7/16	2	2.2577	2.2531	2.4377	2.4365	2.2507	2.2489	WSI-3639-32

iglidur® X Kapitel ► Seite 245

d1	d2	b1	d1 ³⁾		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
1/8	3/16	3/16	.1266	.1247	.1878	.1873	.1243	.1236	XSI-0203-03
1/8	3/16	5/16	.1266	.1247	.1878	.1873	.1243	.1236	XSI-0203-05
1/8	3/16	3/8	.1266	.1247	.1878	.1873	.1243	.1236	XSI-0203-06
3/16	1/4	3/16	.1888	.1869	.2503	.2497	.1865	.1858	XSI-0304-03
3/16	1/4	1/4	.1888	.1869	.2503	.2497	.1865	.1858	XSI-0304-04
3/16	1/4	3/8	.1888	.1869	.2503	.2497	.1865	.1858	XSI-0304-06
3/16	1/4	1/2	.1888	.1869	.2503	.2497	.1865	.1858	XSI-0304-08
1/4	5/16	1/4	.2518	.2495	.3128	.3122	.2490	.2481	XSI-0405-04
1/4	5/16	3/8	.2518	.2495	.3128	.3122	.2490	.2481	XSI-0405-06
1/4	5/16	1/2	.2518	.2495	.3128	.3122	.2490	.2481	XSI-0405-08
5/16	3/8	1/4	.3143	.3120	.3753	.3747	.3115	.3106	XSI-0506-04
5/16	3/8	3/8	.3143	.3120	.3753	.3747	.3115	.3106	XSI-0506-06
5/16	3/8	1/2	.3143	.3120	.3753	.3747	.3115	.3106	XSI-0506-08
3/8	15/32	1/4	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-04
3/8	15/32	5/16	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-05
3/8	15/32	3/8	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-06
3/8	15/32	1/2	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-08
3/8	15/32	5/8	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-10
3/8	15/32	3/4	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-12
7/16	17/32	1/4	.4399	.4371	.5316	.5309	.4365	.4355	XSI-0708-04
7/16	17/32	1/2	.4399	.4371	.5316	.5309	.4365	.4355	XSI-0708-08
7/16	17/32	5/8	.4399	.4371	.5316	.5309	.4365	.4355	XSI-0708-10
7/16	17/32	3/4	.4399	.4371	.5316	.5309	.4365	.4355	XSI-0708-12
1/2	19/32	1/4	.5030	.5003	.5941	.5934	.4990	.4980	XSI-0809-04
1/2	19/32	3/8	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-06
1/2	19/32	1/2	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-08
1/2	19/32	5/8	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-10
1/2	19/32	3/4	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-12
1/2	19/32	1	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-16
9/16	21/32	1/2	.5649	.5620	.6566	.6559	.5615	.5605	XSI-0910-08
9/16	21/32	5/8	.5649	.5620	.6566	.6559	.5615	.5605	XSI-0910-10
9/16	21/32	3/4	.5649	.5620	.6566	.6559	.5615	.5605	XSI-0910-12
5/8	23/32	1/4	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-04
5/8	23/32	3/8	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-06
5/8	23/32	1/2	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-08
5/8	23/32	5/8	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-10
5/8	23/32	3/4	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-12
5/8	23/32	1	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-16
11/16	25/32	7/8	.6906	.6879	.7817	.7809	.6865	.6855	XSI-1112-14
3/4	7/8	3/8	.7532	.7499	.8755	.8747	.7491	.7479	XSI-1214-06

³⁾ nach dem Einpressen. Messverfahren ► Seite 57

d1	d2	b1	d1 ³⁾		Einpressbohrung		Wellenmaße		Art.-Nr.
			max.	min.	max.	min.	max.	min.	
3/4	7/8	1/2	.7532	.7499	.8755	.8747	.7491	.7479	XSI-1214-08
3/4	7/8	3/4	.7532	.7499	.8755	.8747	.7491	.7479	XSI-1214-12
3/4	7/8	1	.7532	.7499	.8755	.8747	.7491	.7479	XSI-1214-16
7/8	1	1/2	.8782	.8749	1.0005	.9997	.8741	.8729	XSI-1416-08
7/8	1	3/4	.8782	.8749	1.0005	.9997	.8741	.8729	XSI-1416-12
7/8	1	1	.8782	.8749	1.0005	.9997	.8741	.8729	XSI-1416-16
1	1 1/8	1/2	1.0032	.9999	1.1255	1.1247	.9991	.9979	XSI-1618-08
1	1 1/8	3/4	1.0032	.9999	1.1255	1.1247	.9991	.9979	XSI-1618-12
1	1 1/8	1	1.0032	.9999	1.1255	1.1247	.9991	.9979	XSI-1618-16
1	1 1/8	1 1/2	1.0032	.9999	1.1255	1.1247	.9991	.9979	XSI-1618-24
1 1/8	1 9/32	3/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	XSI-1820-12
1 1/8	1 9/32	1	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	XSI-1820-16
1 1/8	1 9/32	1 1/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	XSI-1820-20
1 1/4	1 13/32	5/8	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	XSI-2022-10
1 1/4	1 13/32	3/4	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	XSI-2022-12
1 1/4	1 13/32	1	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	XSI-2022-16
1 1/4	1 13/32	1 1/4	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	XSI-2022-20
1 1/2	1 21/32	3/4	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	XSI-2426-12
1 1/2	1 21/32	1	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	XSI-2426-16
1 1/2	1 21/32	1 1/2	1.5037	1.4998	1.6568	1.6558	1.4988	1.4972	XSI-2426-24
1 5/8	1 25/32	1	1.6287	1.6248	1.7818	1.7808	1.6238	1.6222	XSI-2629-16
1 5/8	1 25/32	1 1/4	1.6287	1.6248	1.7818	1.7808	1.6238	1.6222	XSI-2629-20
1 5/8	1 25/32	1 1/2	1.6287	1.6248	1.7818	1.7808	1.6238	1.6222	XSI-2629-24
1 3/4	1 15/16	1	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	XSI-2831-16
1 3/4	1 15/16	2	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	XSI-2831-32
1 7/8	2 1/16	1	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	XSI-3033-16
1 7/8	2 1/16	2	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	XSI-3033-32
2	2 3/16	1	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	XSI-3235-16
2	2 3/16	1 1/2	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	XSI-3235-24
2	2 3/16	2	2.0040	1.9993	2.1883	2.1871	1.9981	1.9969	XSI-3235-32
2 1/4	2 7/16	2	2.2577	2.2531	2.4377	2.4365	2.2507	2.2489	XSI-3639-32
2 3/4	2 15/16	2	2.7570	2.7523	2.9370	2.9358	2.7500	2.7490	XSI-4447-32

³⁾ nach dem Einpressen. Messverfahren ► Seite 57

iglidur® Z										
Kapitel ► Seite 255										
d1	d2	b1	d1 ³⁾		Einpressbohrung		Wellenmaße		Art.-Nr.	
			max.	min.	max.	min.	max.	min.		
1/8	3/16	3/16	.1266	.1247	.1878	.1873	.1243	.1236	ZSI-0203-03	
3/16	1/4	1/4	.1888	.1869	.2503	.2497	.1865	.1858	ZSI-0304-04	
3/16	1/4	3/8	.1888	.1869	.2503	.2497	.1865	.1858	ZSI-0304-06	
1/4	5/16	3/8	.2518	.2495	.3128	.3122	.2490	.2481	ZSI-0405-06	
1/4	5/16	1/2	.2518	.2495	.3128	.3122	.2490	.2481	ZSI-0405-08	
5/16	3/8	1/4	.3143	.3120	.3753	.3747	.3115	.3106	ZSI-0506-04	
5/16	3/8	3/8	.3143	.3120	.3753	.3747	.3115	.3106	ZSI-0506-06	
5/16	3/8	1/2	.3143	.3120	.3753	.3747	.3115	.3106	ZSI-0506-08	
3/8	15/32	1/4	.3768	.3745	.4691	.4684	.3740	.3731	ZSI-0607-04	
3/8	15/32	3/8	.3768	.3745	.4691	.4684	.3740	.3731	ZSI-0607-06	
3/8	15/32	1/2	.3768	.3745	.4691	.4684	.3740	.3731	ZSI-0607-08	
3/8	15/32	5/8	.3768	.3745	.4691	.4684	.3740	.3731	ZSI-0607-10	
3/8	15/32	3/4	.3768	.3745	.4691	.4684	.3740	.3731	ZSI-0607-12	
7/16	17/32	1/2	.4399	.4371	.5316	.5309	.4365	.4355	ZSI-0708-08	
7/16	17/32	3/4	.4399	.4371	.5316	.5309	.4365	.4355	ZSI-0708-12	
1/2	19/32	1/4	.5024	.4996	.5941	.5934	.4990	.4980	ZSI-0809-04	
1/2	19/32	3/8	.5024	.4996	.5941	.5934	.4990	.4980	ZSI-0809-06	
1/2	19/32	1/2	.5024	.4996	.5941	.5934	.4990	.4980	ZSI-0809-08	
1/2	19/32	5/8	.5024	.4996	.5941	.5934	.4990	.4980	ZSI-0809-10	
1/2	19/32	3/4	.5024	.4996	.5941	.5934	.4990	.4980	ZSI-0809-12	
1/2	19/32	1	.5024	.4996	.5941	.5934	.4990	.4980	ZSI-0809-16	
1/2	5/8	3/4	.5034	.5006	.6260	.6250	.5000	.4990	ZSI-0810-12	
9/16	21/32	1/2	.5649	.5620	.6566	.6559	.5615	.5605	ZSI-0910-08	
9/16	21/32	5/8	.5649	.5620	.6566	.6559	.5615	.5605	ZSI-0910-10	
9/16	21/32	3/4	.5649	.5620	.6566	.6559	.5615	.5605	ZSI-0910-12	
5/8	23/32	1/2	.6274	.6246	.7192	.7184	.6240	.6230	ZSI-1011-08	
5/8	23/32	3/4	.6274	.6246	.7192	.7184	.6240	.6230	ZSI-1011-12	
5/8	23/32	1	.6274	.6246	.7192	.7184	.6240	.6230	ZSI-1011-16	
3/4	7/8	1/2	.7532	.7499	.8755	.8747	.7491	.7479	ZSI-1214-08	
3/4	7/8	3/4	.7532	.7499	.8755	.8747	.7491	.7479	ZSI-1214-12	
3/4	7/8	1	.7532	.7499	.8755	.8747	.7491	.7479	ZSI-1214-16	
7/8	1	1/2	.8782	.8749	1.0005	.9997	.8741	.8729	ZSI-1416-08	
7/8	1	3/4	.8782	.8749	1.0005	.9997	.8741	.8729	ZSI-1416-12	
7/8	1	1	.8782	.8749	1.0005	.9997	.8741	.8729	ZSI-1416-16	
1	1 1/8	1/2	1.0032	.9999	1.1255	1.1247	.9991	.9979	ZSI-1618-08	
1	1 1/8	3/4	1.0032	.9999	1.1255	1.1247	.9991	.9979	ZSI-1618-12	
1	1 1/8	1	1.0032	.9999	1.1255	1.1247	.9991	.9979	ZSI-1618-16	
1	1 1/8	1 1/2	1.0032	.9999	1.1255	1.1247	.9991	.9979	ZSI-1618-24	
1 1/8	1 1/4	3/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	ZSI-1820-12	
1 1/8	1 1/4	1	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	ZSI-1820-16	
1 1/8	1 1/4	1 1/4	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	ZSI-1820-20	
1 1/8	1 9/32	1 1/2	1.1279	1.1246	1.2818	1.2808	1.1238	1.1226	ZSI-1820-24	
1 1/4	1 13/32	3/4	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	ZSI-2022-12	
1 1/4	1 13/32	1	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	ZSI-2022-16	

³⁾ nach dem Einpressen. Messverfahren ► Seite 57