


标准液压夹紧缸




允许的压力最大为 120 bar 时，拉力最大 23 kN

订货号	有效方向名称	H [mm]	油 [cm ³]	D [mm]	d [mm]	连接螺纹	L [mm]			重量 [kg]		
							①	②*	③			
507	SPZ.5xx-d2.5	2.5	5.2	102	22	M24x1.5	60	149		2.90		
	SPZ.5xx-9	9	18.8				72	161		2.85		
	SPZ.5xx-15	15								3.44		
	SPZ.507-WMS2						•					
510	SPZ.5xx-d2.5	2.5	5.2	102	22	M24x1.5	52	141	136	2.90		
	SPZ.5xx-9	9	18.8				64	153	148	2.85		
	SPZ.5xx-15	15								3.44		
	SPZ.510-WMS2									•		
	SPZ.510-WMS7							•	0.21			
520	SPZ.520-d2.5	2.5	5.2	102	22	M24x1.5	73	165	160	3.60		
	SPZ.520-9	9	18.8				85	177	172	3.55		
	SPZ.520-15	15								4.14		
	SPZ.520-WMS2									•		
	SPZ.520-WMS7							•				
530	SPZ.530-d2.5	2.5	5.2	102	22	M24x1.5	65	144	133	5.09		
	SPZ.530-9	9	18.8				77	156	145	5.04		
	SPZ.530-15	15								5.63		
	SPZ.530-WMS2									•		
	SPZ.530-WMS7										•	
所有型号	SPZ.Awk-Vor	存在检测准备 (控制箱, 可选, SPZ.Awk)										
	SPZ.Awk	工件在位检测的控制箱含 10m 软管材料和穿墙套管 (连接前面的 SPZ.Awk)										

* 如欲与 pL 配件组合请另行咨询 (仅适合行程 2.5mm 和 9mm)

功能原理



在液压方面：力图 10...120 bar (压力或拉力；恰当的液压机组第 75 页)

