

## SERIES 71



**GREY NON-MARKING THERMOPLASTIC RUBBER WHEELS,  
POLYPROPYLENE CENTRE,  
SWIVEL BOLT HOLE BRACKET TYPE "NL"**

### Wheel description




**Tread:** grey non-marking thermoplastic rubber tread, hardness 85+/-4 Shore A; excellent rolling resistance and elasticity.

**Centre:** polypropylene.

**Hub:** the hub is available with plain bearing, with roller bearing and with double shielding ball bearing, coprinted in the centre of the wheel.

### Bracket description

**Standard duty bracket type NL (max. carrying capacity 400 daN)**



1) **Plate:** electrolytically galvanised steel plate

2) **Fork:** electrolytically galvanised steel plate

3) **Ball Racing Ring:** electrolytically galvanised steel plate

4) **King Pin:** incorporated in top plate and cold riveted

5) **Swivel actions:** double ring of greased balls

**Finishing:** electrolytic galvanisation

**Fitting:** bolt hole